



# CoroMill® 390 square shoulder milling cutter

Arbor

Long edge

STDNO  
KAPR

ISO 6462:2011  
90°



## Metric version

DC	CZC <sub>MS</sub>	APMX	CNSC	Ordering code	Dimensions								CICT	MID		
					DCON	ISO	DBC	DCX	LF	Nm	kg	RPMX				
40.0	11	16	36.0	0	3	R390-040Q16-36M	16.0	A		40.0	56.7	1.2	0.80	18900	12	R390-11..
	11	16	36.0	0	4	R390-040Q16-36H	16.0	A		40.0	56.7	1.2	0.80	18900	16	R390-11..
44.0	11	16	45.0	0	3	R390-044Q16-45M	16.0	A		44.0	65.5	1.2	0.98	17800	15	R390-11..
	18	16	43.0	0	2	R390-044Q16-43L	16.0	A		44.0	68.6	3.0	0.83	8600	6	R390-18..
50.0	11	22	54.0	0	3	R390-050Q22-54L	22.0	A		50.0	74.4	1.2	1.08	16600	18	R390-11..
	11	22	36.0	0	4	R390-050Q22-36M	22.0	A		50.0	56.7	1.2	0.99	16600	16	R390-11..
	11	22	36.0	0	5	R390-050Q22-36H	22.0	A		50.0	56.7	1.2	0.99	16600	20	R390-11..
	18	22	57.0	0	2	R390-050Q22-57L	22.0	A		50.0	82.6	3.0	1.08	7900	8	R390-18..
54.0	11	22	36.0	0	4	R390-054Q22-36M	22.0	A		54.0	56.7	1.2	0.99	16000	16	R390-11..
	18	22	57.0	0	2	R390-054Q22-57L	22.0	A		54.0	82.6	3.0	1.20	7500	8	R390-18..
63.0	18	27	57.0	0	3	R390-063Q27-57L	27.0	A		63.0	82.6	3.0	1.06	6800	12	R390-18..
80.0	18	32	71.0	0	3	R390-080Q32-71L	32.0	A		80.0	96.7	3.0	2.70	5900	15	R390-18..
100.0	18	40	57.0	0	4	R390-100Q40-57M	40.0	B		100.0	82.6	3.0	3.18	5200	16	R390-18..
125.0	18	40	43.0	0	6	R390-125Q40-43L	40.0	B		125.0	68.6	3.0	4.72	4600	18	R390-18..
160.0	18	40S	43.0	0	8	R390-160Q40-43L	40.0	C	66.7	160.0	68.6	3.0	8.50	4000	24	R390-18..
200.0	18	60	43.0	0	9	R390-200Q60-43L	60.0	C	101.6	200.0	68.6	3.0	9.80	3600	27	R390-18..

