






CoroMill® 300 insert for milling



Metric version

	RE	Ordering code	P		M		K		N		S		H		Dimensions, mm, inch													
			1025	1030	4220	4230	4240	1030	1040	2030	2040	1020	3040	3330	4220	4240	HT3A	1025	1030	1010	1025	1030	4220	IC	S			
			1025	1030	4220	4230	4240	1030	1040	2030	2040	1020	3040	3330	4220	4240	HT3A	1025	1030	1010	1025	1030	4220	IC	S			
Medium		08 4.0 R300-0828E-MM																							8.0	2.78		
		.157						*																		.315	.109	
		10 5.0 R300-1032E-MM						*						*												10.0	3.18	
		.197						*						*													.394	.125
		12 6.0 R300-1240E-MM						*	*	*			*	*													12.0	3.97
		.236						*	*	*			*	*													.472	.156
		16 8.0 R300-1648E-MM						*	*			*	*													16.0	4.76	
		.315						*	*			*	*														.630	.187
		20 10.0 R300-2060E-MM						*	*	*			*	*													20.0	6.48
		.394						*	*	*			*	*													.787	.255
		08 4.0 R300-0828M-MM						*	*	*			*	*													8.0	2.78
		.157						*	*	*			*	*													.315	.109
Heavy		10 5.0 R300-1032M-MM						*				*	*												10.0	3.18		
		.197						*				*	*														.394	.125
		12 6.0 R300-1240M-MM						*	*	*			*	*													12.0	3.97
		.236						*	*	*			*	*													.472	.156
		16 8.0 R300-1648M-MM						*	*	*			*	*													16.0	4.76
		.315						*	*	*			*	*													.630	.187
		20 10.0 R300-2060M-MM						*	*	*			*	*													20.0	6.48
		.394						*	*	*			*	*													.787	.255
		08 4.0 R300-0828M-MH							*				*														8.0	2.78
		.157							*				*														.315	.109
		10 5.0 R300-1032M-MH							*	*			*	*													10.0	3.18
		.197							*	*			*	*														.394



J474



J508



Q1



Q17

