



CoroMill® 300 face milling cutter

Threaded coupling

Neutral design



Metric version

										Dimensions									
DC		CZC _{MS}	APMX _{EFW}	APMX _{FFW}	AZ	RMPX	CNSC		Ordering code	DCON	DCX	LF	LU			RPMX	CICT	MIID	
5.0	05	M8	3.8	2.5	1.8	20°	0	2	R300-10T08-05L	12.8	10.0	42.5	14.8	0.6	0.10	1000	2	R300-0517..	
	07	20	M8	5.3	3.5	1.0	20°	0	2	R300-12T08-07L	12.8	12.0	42.5	17.3	0.9	0.10	1000	2	R300-0720..
7.0	05	M8	3.8	2.5	1.0	10°	0	3	R300-12T08-05M	12.8	12.0	42.5		0.6	0.10	1000	3	R300-0517..	
8.0	07	20	M8	5.3	3.5	1.1	20°	0	3	R300-15T08-07M	12.8	15.0	42.5		0.9	0.10	1000	3	R300-0720..
	07	24	M8	5.3	3.5	0.9	20°	0	2	R300-15T08-07L	12.8	15.0	42.5		0.9	0.10	1000	2	R300-0724..
	08	M8	6.0	4.0	1.8	20°	0	2	R300-16T08-08L	12.8	16.0	42.5		1.2	0.10	1000	2	R300-0828..	
9.0	07	20	M8	5.3	3.5	0.9	15°	0	3	R300-16T08-07M	12.8	16.0	42.5		0.9	0.10	1000	3	R300-0720..
10.0	10	M10	7.5	5.0	3.4	20°	1	2	R300-20T10-10L	17.8	20.0	49.5		3.0	0.20	1000	2	R300-1032..	
12.0	08	M10	6.0	4.0	1.5	12°	1	3	R300-20T10-08M	17.8	20.0	49.5		1.2	0.15	1000	3	R300-0828..	
	12	M12	9.0	6.0	2.7	20°	1	2	R300-24T12-12L	20.8	24.0	57.0		3.0	0.20	1000	2	R300-1240..	
15.0	10	M12	7.5	5.0	1.3	15°	1	3	R300-25T12-10M	20.8	25.0	57.0		3.0	0.20	1000	3	R300-1032..	
	10	M12	7.5	5.0	1.1	15°	1	2	R300-25T12-10L	20.8	25.0	57.0		3.0	0.20	1000	2	R300-1032..	
16.0	16	M16	12.0	8.0	4.8	20°	1	2	R300-32T16-16L	28.8	32.0	69.0		5.0	0.24	1000	2	R300-1648..	
20.0	12	M16	9.0	6.0	1.4	15°	1	3	R300-32T16-12M	28.8	32.0	69.0		3.0	0.24	1000	3	R300-1240..	
22.0	10	M16	7.5	5.0	1.7	10°	1	4	R300-32T16-10H	28.8	32.0	69.0		3.0	0.24	1000	4	R300-1032..	
23.0	12	M16	9.0	6.0	5.0	16°	1	3	R300-35T16-12M	28.8	35.0	69.0		3.0	0.34	1000	3	R300-1240..	
25.0	10	M16	7.5	5.0	3.6	10°	1	4	R300-35T16-10H	28.8	35.0	69.0		3.0	0.38	1000	4	R300-1032..	
28.0	12	M16	9.0	6.0	5.0	13°	1	4	R300-40T16-12M	28.8	40.0	69.0		3.0	0.38	1000	4	R300-1240..	
30.0	10	M16	7.5	5.0	3.6	8°	1	5	R300-40T16-10H	28.8	40.0	69.0		3.0	0.38	1000	5	R300-1032..	
	12	M16	9.0	6.0	5.0	12°	1	4	R300-42T16-12M	28.8	42.0	69.0		3.0	0.38	1000	4	R300-1240..	
32.0	10	M16	7.5	5.0	3.6	7°	1	5	R300-42T16-10H	28.8	42.0	69.0		3.0	0.38	1000	5	R300-1032..	

Inch version

										Dimensions, inch								
DC		CZC _{MS}	APMX _{EFW}	APMX _{FFW}	AZ	RMPX	CNSC		Ordering code	DCON	DCX	LF	LU			RPMX	CICT	MIID
.310	08	M8	.236	.157	.039	20°	0	2	RA300-16T08-08L	.504	.625	1.594	0.9	0.66		1000	2	R300-08..
.356	10	M10	.295	.197	.110	20°	1	2	RA300-19T10-10L	.701	.750	1.949	2.2	0.66		1000	2	R300-10..



J200



O5



Q5



Q1



Q35



Q16