


**CoroMill® 200 insert for milling**



**Metric version**

	RE	Ordering code	P				M				K				N				S				H				Dimensions, mm, inch																	
			1025	1030	4220	4230	4240	530	1025	1030	1040	2030	2040	235	530	1020	3040	3220	3330	4220	4230	4240	1025	1030	1010	1025	1030	2030	2040	HI0F	HI3A	SS30T	S40T	1010	1025	1030	3040	4220	530	IC	S			
Medium	10 .197	RCKT 10 T3 M0-WM				☆					☆																													10.0	3.97			
	12 .236	RCKT 12 04 M0-WM					☆																																		12.0	4.76		
	16 .315	RCKT 16 06 M0-WM																																								16.0	6.35	
	20 .394	RCKT 20 06 M0-WM																																									20.0	6.35
	10 .197	RCKT 10 T3 M0-PH	☆	☆	☆	☆		☆												☆																		☆				10.0	3.97	
12 .236	RCKT 12 04 M0-PH	☆	☆	☆	☆		☆												☆																		☆					12.0	4.76	
16 .315	RCKT 16 06 M0-PH	☆	☆	☆	☆		☆												☆																		☆					16.0	6.35	
20 .394	RCKT 20 06 M0-PH	☆	☆	☆	☆		☆												☆																		☆					20.0	6.35	
10 .197	RCKT 10 T3 M0-KH															☆	☆	☆	☆																		☆				10.0	3.97		
12 .236	RCKT 12 04 M0-KH															☆	☆	☆	☆																		☆				12.0	4.76		
16 .315	RCKT 16 06 M0-KH															☆	☆	☆	☆																		☆				16.0	6.35		
20 .394	RCKT 20 06 M0-KH															☆	☆	☆	☆																		☆				20.0	6.35		

