



CoroMill® 200 face milling cutter

Cylindrical shank



Metric version

										Dimensions							
DC	CZC _{MS}	APM _{EFW}	APM _{FFW}	AZ	RMPX	CNSC	Ordering code			DCON	DCX	LF	Nm	Kg	RPMX	CICT	MID
15.0	10	20	7.5	5.0	2.9	13°	0	3	R200-015A20-10H	20.0	25.0	150.0	3.0	0.48	37500	3	RCKT 10 T3 M0
	10	20	7.5	5.0	2.9	13°	0	2	R200-015A20-10M	20.0	25.0	150.0	3.0	0.54	37500	2	RCKT 10 T3 M0
20.0	12	25	9.0	6.0	3.7	13°	0	3	R200-020A25-12H	25.0	32.0	190.0	3.0	0.83	31100	3	RCKT 12 04 M0
	12	25	9.0	6.0	3.7	13°	0	2	R200-020A25-12M	25.0	32.0	190.0	3.0	0.84	31100	2	RCKT 12 04 M0
24.0	16	32	12.0	8.0	4.9	13°	0	2	R200-024A32-16L	32.0	40.0	240.0	5.0	1.42	21800	2	RCKT 16 06 M0
	16	32	12.0	8.0	4.9	13°	0	3	R200-024A32-16M	32.0	40.0	240.0	5.0	1.42	21800	3	RCKT 16 06 M0
28.0	12	32	9.0	6.0	3.7	9°	0	2	R200-028A32-12L	32.0	40.0	240.0	3.0	1.82	26300	2	RCKT 12 04 M0
	12	32	9.0	6.0	3.7	9°	0	3	R200-028A32-12M	32.0	40.0	240.0	3.0	1.82	26300	3	RCKT 12 04 M0
30.0	20	32	15.0	10.0	6.1	13°	0	2	R200-030A32-20L	32.0	50.0	240.0	7.5	1.82	20900	2	RCKT 20 06 M0
	20	32	15.0	10.0	6.1	13°	0	3	R200-030A32-20M	32.0	50.0	240.0	7.5	1.82	20900	3	RCKT 20 06 M0
34.0	16	32	12.0	8.0	4.9	11°	0	3	R200-034A32-16M	32.0	50.0	240.0	5.0	1.83	18300	3	RCKT 16 06 M0
38.0	12	32	9.0	6.0	3.7	6°	0	3	R200-038A32-12L	32.0	50.0	240.0	3.0	1.84	22500	3	RCKT 12 04 M0
	12	32	9.0	6.0	3.7	6°	0	4	R200-038A32-12M	32.0	50.0	240.0	3.0	1.84	22500	4	RCKT 12 04 M0

