


CoroMill® 329 groove milling cutter

Arbor

Positive geometry

STDNO
KAPR

ISO 6462:2011
90°



Metric version

										Dimensions									
CW	DC	CDX	SSC	CZC _{MS}	APMX	CNSC		Ordering code		DCON	ISO	LF	LU	DHUB		RPMX	CICT	MIID	
2.0	100	15.0	E	22	2.0	0	6	329-100Q22-E		22.0	A	50.0		43.0	1.10	4700	6	N123E2-0200-	
	125	18.0	E	32	2.0	0	9	329-125Q32-E		32.0	A	63.0	32	60.0	1.69	4100	9	N123E2-0200-	
2.5	100	15.0	F	22	2.5	0	6	329-100Q22-F		22.0	A	50.0	17	42.0	1.05	4400	6	N123F2-0250-	
	125	18.0	F	32	2.5	0	9	329-125Q32-F		32.0	A	63.0		60.0	1.76	3800	9	N123F2-0250-	
3.0	100	15.0	G	22	3.0	0	6	329-100Q22-G		22.0	A	50.0	17	42.0	1.04	4300	6	N123G2-0300-	
	125	18.0	G	32	3.0	0	8	329-125Q32-G		32.0	A	63.0		60.0	1.77	3700	8	N123G2-0300-	
	160	18.0	G	40	3.0	0	11	329-160Q40-G		40.0	B	63.0		72.0	2.06	3300	11	N123G2-0300-	
4.0	100	15.0	H	22	4.0	0	6	329-100Q22-H		22.0	A	50.0		42.0	1.09	3600	6	N123H2-0400-	
	125	18.0	H	32	4.0	0	8	329-125Q32-H		32.0	A	63.0	35	63.0	1.78	3150	8	N123H2-0400-	
5.0	100	15.0	J	22	5.0	0	6	329-100Q22-J		22.0	A	50.0	19	43.0	1.11	3350	6	N123J2-0500-	
	125	18.0	J	32	5.0	0	7	329-125Q32-J		32.0	A	63.0	30	63.0	1.81	2900	7	N123J2-0500-	

Inch version

										Dimensions, inch									
CW	DC	CDX	SSC	CZC _{MS}	APMX	CNSC		Ordering code		DCON	ISO	LF	LU	DHUB		RPMX	CICT	MIID	
.079	4.000	.591	E	1	.079	0	6	A329-102R25-E		1.000	A	1.969	.669	1.969	2.38	4700	6	N123E2-0200-	
	5.000	.709	E	1 1/4	.079	0	9	A329-127R32-E		1.250	A	2.481		2.362	2.64	4100	9	N123E2-0200-	
.098	4.000	.591	F	1	.098	0	5	A329-102R25-F		1.000	A	1.969	.531	1.969	2.51	4300	5	N123F2-0250-	
	5.000	.709	F	1 1/4	.098	0	9	A329-127R32-F		1.250	A	2.481		2.362	3.91	3700	9	N123F2-0250-	
.118	4.000	.591	G	1	.118	0	6	A329-102R25-G		1.000	A	1.969	.630	1.969	2.51	4200	6	N123G2-0300-	
	5.000	.709	G	1 1/4	.118	0	8	A329-127R32-G		1.250	A	2.481		2.362	3.96	3600	8	N123G2-0300-	
.157	4.000	.591	H	3/4	.157	0	6	A329-102R19-H		.750	A	1.969		1.654	2.42	3500	6	N123H2-0400-	
	5.000	.709	H	1 1/4	.157	0	8	A329-127R32-H		1.250	A	2.481	1.378	2.480	3.82	3050	8	N123H2-0400-	
.197	4.000	.591	J	3/4	.197	0	6	A329-102R19-J		.750	A	1.969	.768	1.693	2.07	3350	6	N123J2-0500-	
	5.000	.709	J	1 1/4	.197	0	7	A329-127R32-J		1.250	A	2.481	1.181	2.480	2.64	2900	7	N123J2-0500-	

