



CoroMill® 316 solid carbide head for square shoulder milling

Straight corner radius, center cut

End mills with chip-breaker profile

CNSC 316..SM..K
 FHA 0
 BSG 45°
 TCDC COROMANT
 h12



Metric version

DC	CZC _{MS}	APMX	RE	ZEFP	Ordering code	P	M	K	S	Dimensions		
						1030	1030	1030	1030	DCON	LF	DN
10.0	E10	5.5	0.40	5	316-10SM545-10004K	☆	☆	☆	☆	9.7	12.4	9.7
	E10	5.5	0.40	4	316-10SM440-10004K	☆	☆	☆	☆	9.7	12.4	9.7
12.0	E12	6.5	0.40	4	316-12SM440-12004K	☆	☆	☆	☆	11.7	14.5	11.7
	E12	6.5	0.40	5	316-12SM545-12004K	☆	☆	☆	☆	11.7	14.5	11.7
16.0	E16	8.5	0.40	4	316-16SM440-16004K	☆	☆	☆	☆	15.5	18.7	15.5
	E16	8.5	0.40	6	316-16SM645-16004K	☆	☆	☆	☆	15.5	18.7	15.5
25.0	E25	13.5	0.40	8	316-25SM845-25004K	☆	☆	☆	☆	24.2	25.6	24.2

Inch version

DC	CZC _{MS}	APMX	RE	ZEFP	Ordering code	P	M	K	S	Dimensions, inch		
						1030	1030	1030	1030	DCON	LF	DN
.375	E10	.209	.016	4	A316-10SM440-03704K	☆	☆	☆	☆	.364	.488	.364
.500	E12	.276	.016	4	A316-12SM440-05004K	☆	☆	☆	☆	.484	.575	.484
	E12	.276	.062	4	A316-12SM440-05015K	☆	☆	☆	☆	.484	.575	.484
.625	E16	.335	.016	4	A316-16SM440-06204K	☆	☆	☆	☆	.610	.736	.610
	E16	.335	.062	4	A316-16SM440-06215K	☆	☆	☆	☆	.610	.736	.610
.750	E20	.413	.015	4	A316-20SM440-07504K	☆	☆	☆	☆	.728	.839	.728
	E20	.413	.016	6	A316-20SM645-07504K	☆	☆	☆	☆	.728	.839	.728
1.000	E25	.551	.016	8	A316-25SM845-10004K	☆	☆	☆	☆	.965	1.008	.965



E3



A233



A244



G2



G30



G24