



CoroMill® Plura solid carbide square shoulder end mill

Straight, center cut

End mills for heavy duty milling

CNSC 1
 FHA 38°
 BSG COROMANT
 TCDC h10
 TCDCON h6



Metric version

| DC | CZC _{MS} | APMX | CHW | KCH | LU | ZEFP | Ordering code | M S | | Dimensions | | |
|------|-------------------|------|------|-----|------|------|----------------|------|------|------------|-------|--------|
| | | | | | | | | 1740 | 1740 | DCON | LF | CP Bar |
| 6.0 | 6 | 13.0 | 0.10 | 45° | 13.0 | 4 | 2P342-0600-CMA | ☆ | ☆ | 6.0 | 57.0 | 20 |
| 8.0 | 8 | 18.0 | 0.15 | 45° | 18.0 | 4 | 2P342-0800-CMA | ☆ | ☆ | 8.0 | 63.0 | 20 |
| 10.0 | 10 | 22.0 | 0.15 | 45° | 22.0 | 4 | 2P342-1000-CMA | ☆ | ☆ | 10.0 | 72.0 | 20 |
| 12.0 | 12 | 26.0 | 0.15 | 45° | 26.0 | 4 | 2P342-1200-CMA | ☆ | ☆ | 12.0 | 83.0 | 20 |
| 16.0 | 16 | 34.0 | 0.25 | 45° | 34.0 | 4 | 2P342-1600-CMA | ☆ | ☆ | 16.0 | 92.0 | 20 |
| 20.0 | 20 | 42.0 | 0.25 | 45° | 42.0 | 4 | 2P342-2000-CMA | ☆ | ☆ | 20.0 | 104.0 | 20 |
| 25.0 | 25 | 52.0 | 0.25 | 45° | 52.0 | 4 | 2P342-2500-CMA | ☆ | ☆ | 25.0 | 121.0 | 20 |

Inch version

| DC | CZC _{MS} | APMX | CHW | KCH | LU | ZEFP | Ordering code | M S | | Dimensions, inch | | |
|------|-------------------|-------|------|-----|-------|------|----------------|------|------|------------------|-------|--------|
| | | | | | | | | 1740 | 1740 | DCON | LF | CP Bar |
| .250 | 1/4 | .625 | .004 | 45° | .625 | 4 | 2P342-0635-CMA | ☆ | ☆ | .250 | 2.500 | 290 |
| .313 | 5/16 | .750 | .004 | 45° | .750 | 4 | 2P342-0794-CMA | ☆ | ☆ | .313 | 2.500 | 290 |
| .375 | 3/8 | .875 | .006 | 45° | .875 | 4 | 2P342-0953-CMA | ☆ | ☆ | .375 | 2.500 | 290 |
| .500 | 1/2 | 1.125 | .006 | 45° | 1.125 | 4 | 2P342-1270-CMA | ☆ | ☆ | .500 | 3.000 | 290 |
| .625 | 5/8 | 1.313 | .010 | 45° | 1.313 | 4 | 2P342-1588-CMA | ☆ | ☆ | .625 | 3.500 | 290 |
| .750 | 3/4 | 1.625 | .010 | 45° | 1.625 | 4 | 2P342-1905-CMA | ☆ | ☆ | .750 | 4.000 | 290 |

