



T-Max® P insert for turning

Rhombic 80°



		ISO CODE	P										M					K					S					ANSI CODE		
			1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	H13A	1105	1115	1125	GC15		H13A	S05F
Roughing		12 1/2	CNMM 12 04 08-MR																											CNMM 432-MR
			CNMM 12 04 12-MR											☆	☆															CNMM 433-MR
			CNMM 12 04 16-MR											☆	☆															CNMM 434-MR
		16 5/8	CNMM 16 06 12-MR											☆	☆															CNMM 543-MR
			CNMM 16 06 16-MR											☆	☆															CNMM 544-MR
			CNMM 16 06 24-MR											☆	☆															CNMM 643-MR
		19 3/4	CNMM 19 06 12-MR											☆	☆															CNMM 644-MR
			CNMM 19 06 16-MR											☆	☆															CNMM 646-MR
			CNMM 19 06 24-MR											☆	☆															CNMM 866-MR
		25 1	CNMM 25 09 24-MR				☆							☆	☆															CNMM 866-MR
			12 1/2	CNMG 12 04 08-KRR															☆	☆	☆									CNMG 432-KRR
				CNMG 12 04 12-KRR																☆	☆	☆								
			CNMG 12 04 16-KRR																☆	☆	☆									CNMG 434-KRR
		16 5/8	CNMG 16 06 12-KRR																☆	☆	☆									CNMG 543-KRR
			CNMG 16 06 16-KRR																☆	☆	☆									CNMG 544-KRR
			CNMG 16 06 24-KRR																☆	☆	☆									
		12 1/2	CNMM 12 04 08-WR				☆	☆	☆	☆																				CNMM 432-WR
			CNMM 12 04 12-WR				☆	☆	☆	☆																				CNMM 433-WR
			CNMM 12 04 16-WR				☆	☆	☆	☆																				CNMM 434-WR
		16 5/8	CNMM 16 06 12-WR				☆	☆	☆	☆																				CNMM 543-WR
		CNMM 16 06 16-WR				☆	☆	☆	☆																				CNMM 544-WR	
		CNMM 16 06 24-WR				☆	☆	☆	☆																				CNMM 644-WR	
	19 3/4	CNMM 19 06 16-WR				☆	☆	☆	☆																				CNMM 644-WR	
		12 1/2	CNMG 12 04 08-PR				☆	☆	☆	☆																			CNMG 432-PR	
			CNMG 12 04 12-PR				☆	☆	☆	☆																				CNMG 433-PR
		CNMG 12 04 16-PR				☆	☆	☆	☆																				CNMG 434-PR	
	16 5/8	CNMG 16 06 08-PR				☆	☆	☆	☆																				CNMG 542-PR	
		CNMG 16 06 12-PR				☆	☆	☆	☆																				CNMG 543-PR	
		CNMG 16 06 16-PR				☆	☆	☆	☆																				CNMG 544-PR	
		CNMG 16 06 24-PR				☆	☆	☆	☆																				CNMG 546-PR	
		19 3/4	CNMG 19 06 08-PR				☆	☆	☆	☆																			CNMG 642-PR	
			CNMG 19 06 12-PR				☆	☆	☆	☆																				CNMG 643-PR
		CNMG 19 06 16-PR				☆	☆	☆	☆																				CNMG 644-PR	
		CNMG 19 06 24-PR				☆	☆	☆	☆																				CNMG 646-PR	
		25 1	CNMG 25 09 24-PR				☆	☆	☆	☆																			CNMG 866-PR	
			12 1/2	CNMM 12 04 08-PR				☆	☆	☆	☆																			CNMM 432-PR
			CNMM 12 04 12-PR				☆	☆	☆	☆																				CNMM 433-PR
	CNMM 12 04 16-PR					☆	☆	☆	☆																				CNMM 434-PR	
	16 5/8	CNMM 16 06 08-PR				☆	☆	☆	☆																				CNMM 542-PR	
		CNMM 16 06 12-PR				☆	☆	☆	☆																				CNMM 543-PR	
		CNMM 16 06 16-PR				☆	☆	☆	☆																				CNMM 544-PR	
	19 3/4	CNMM 19 06 12-PR				☆	☆	☆	☆																				CNMM 643-PR	
		CNMM 19 06 16-PR				☆	☆	☆	☆																				CNMM 644-PR	
		CNMM 19 06 24-PR				☆	☆	☆	☆																				CNMM 646-PR	

For dimensions, see code key on page I14.



I1