


T-Max® P insert for turning

Rhombic 35°
Advanced cutting materials



	LE	LE"	ISO CODE	H			ANSI CODE
				6050	7015	7025	
 Finishing	16 3/8	2.1 .083	VNGA160404S01020A		☆		VNGA331S0320A
		4.4 .173	VNGA160404S01030A		☆		VNGA331S0330A
		2.4 .094	VNGA160408S01020A		☆		VNGA332S0320A
		3.5 .138	VNGA160408S01030A		☆		VNGA332S0330A
		2.4 .094	VNGA160408S02035A		☆		VNGA332S0835A
	16 3/8	16.2 .638	VNGA160404S01525	☆			VNGA331S0625
		15.8 .622	VNGA160408S01525	☆			VNGA332S0625
		15.8 .622	VNGA160408T01525	☆			VNGA332T0625
		15.4 .607	VNGA160412S01525	☆			VNGA333S0625

For dimensions, see code key on page I14.

