


T-Max® P insert for turning

Triangular



C

	ISO CODE	P								M					K			S				ANSI CODE									
		1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30		H13A	1105	1115	1125	GC15	H13A	S05F		
	16 3/8	TNMG 16 04 08-KM															☆	☆	☆	☆										TNMG 332-KM	
		TNMG 16 04 12-KM															☆	☆	☆	☆										TNMG 333-KM	
	22 1/2	TNMG 22 04 08-KM																☆	☆	☆											TNMG 432-KM
		TNMG 22 04 12-KM																☆	☆	☆											TNMG 433-KM
		TNMG 22 04 16-KM															☆	☆	☆											TNMG 434-KM	
	11 1/4	TNMG 11 03 04-QM				☆	☆	☆																						TNMG 221-QM	
		TNMG 11 03 08-QM			☆	☆	☆	☆																						TNMG 222-QM	
	16 3/8	TNMG 16 03 04-QM																												TNMG 321-QM	
		TNMG 16 03 08-QM																												TNMG 322-QM	
		TNMG 16 04 04-QM				☆	☆	☆	☆															☆				☆		TNMG 331-QM	
		TNMG 16 04 08-QM			☆	☆	☆	☆	☆			☆												☆	☆			☆		TNMG 332-QM	
		TNMG 16 04 12-QM			☆	☆	☆	☆	☆			☆												☆	☆			☆		TNMG 333-QM	
	22 1/2	TNMG 22 04 04-QM				☆	☆	☆																☆				☆		TNMG 431-QM	
		TNMG 22 04 08-QM			☆	☆	☆	☆																☆				☆		TNMG 432-QM	
		TNMG 22 04 12-QM			☆	☆	☆	☆																☆				☆		TNMG 433-QM	
	TNMG 22 04 16-QM			☆	☆	☆	☆																☆	☆			☆		TNMG 434-QM		
	16 3/8	TNMG 16 04 08-SM								☆	☆													☆	☆	☆	☆	☆	TNMG 332-SM		
		TNMG 16 04 12-SM								☆	☆													☆	☆	☆	☆	☆	TNMG 333-SM		
	22 1/2	TNMG 22 04 08-SM								☆	☆													☆	☆	☆	☆	☆	TNMG 432-SM		
		TNMG 22 04 12-SM								☆	☆													☆	☆	☆	☆	☆	TNMG 433-SM		
	27 5/8	TNMG 27 06 12-HM			☆	☆	☆																						TNMG 543-HM		
		TNMG 27 06 16-HM			☆	☆	☆	☆																					TNMG 544-HM		
	33 3/4	TNMG 33 09 24-HM			☆	☆	☆	☆																					TNMG 666-HM		
	16 3/8	TNMG 16 04 12-KM																	☆										TNMG 333-KM		

For dimensions, see code key on page I14.

H

