


T-Max® P shank tool for turning


Rigid clamp design




KAPR
PSIR



DCBNR/L
75°
15°



DCRNR/L
75°
15°



- CNMM, CNGP
- CNMG
- CNMA, CNGA

Metric version

	CZC _{MS}	OHX	CNSC	Ordering code	Dimensions					N _m	Kg	MIID		
					B	H	LF	WF	HF					
	12	20 x 20	34	0	DCBNR/L 2020K 12	20	20	125	17	20	3.9	0.42	CNMG 12 04 08	
		25 x 25	34	0	DCBNR/L 2525M 12	25	25	150	22	25	3.9	0.72	CNMG 12 04 08	
		32 x 25	34	0	DCBNR/L 3225P 12	25	32	170	22	32	3.9	1.10	CNMG 12 04 08	
		32 x 32	34	0	DCBNR/L 3232P 12	32	32	170	27	32	3.9	1.30	CNMG 12 04 08	
		40 x 40	34	0	DCBNR/L 4040S 12	40	40	250	35	40	3.9	3.30	CNMG 12 04 08	
		16	25 x 25	41	0	DCBNR/L 2525M 16	25	25	150	22	25	6.4	0.72	CNMG 16 06 12
			32 x 25	32	0	DCBNR/L 3225P 16	25	32	170	22	32	6.4	1.10	CNMG 16 06 12
			32 x 32	41	0	DCBNR/L 3232P 16	32	32	170	27	32	6.4	1.30	CNMG 16 06 12
			40 x 40	42	0	DCBNR/L 4040S 16	40	40	250	35	40	6.4	3.30	CNMG 16 06 12
		19	32 x 32	46	0	DCBNR/L 3232P 19	32	32	170	27	32	6.4	1.30	CNMG 19 06 12
			40 x 40	46	0	DCBNR/L 4040S 19	40	40	250	35	40	6.4	3.30	CNMG 19 06 12

Inch version

	CZC _{MS}	OHX	CNSC	Ordering code	Dimensions, inch					Ft/lbs	Lbs	MIID		
					B	H	LF	WF	HF					
	1/2	3/4 x 3/4	1.350	0	DCRNR/L 12 4BM1	.750	.750	4.500	.855	.750	2.9	.75	CNMG 432	
		1 x 1	1.350	0	DCRNR/L 16 4DM1	1.000	1.000	6.000	1.048	1.000	2.9	1.98	CNMG 432	
		1 1/4 x 1 1/4	1.350	0	DCRNR/L 20 4DM1	1.250	1.250	6.000	1.292	1.250	2.9	2.42	CNMG 432	
		1 1/2 x 1 1/2	1.350	0	DCRNR/L 24 4DM1	1.500	1.500	6.000	1.697	1.500	2.9	3.78	CNMG 432	
		1 1/4 x 1	1.360	0	DCRNR/L 85 4D	1.000	1.250	6.000	1.047	1.250	2.9	3.78	CNMG 432	
		5/8	1 x 1	1.640	0	DCRNR/L 16 5D	1.000	1.000	6.000	1.047	1.000	4.7	3.78	CNMG 543
			1 1/4 x 1 1/4	1.640	0	DCRNR/L 20 5D	1.250	1.250	6.000	1.291	1.250	4.7	2.42	CNMG 543
			1 1/2 x 1 1/2	1.640	0	DCRNR/L 24 5D	1.500	1.500	6.000	1.697	1.500	4.7	14.52	CNMG 543
			1 1/4 x 1	1.640	0	DCRNR/L 85 5D	1.000	1.250	6.000	1.047	1.250	4.7	3.76	CNMG 543
		3/4	1 1/4 x 1 1/4	1.820	0	DCRNR/L 20 6D	1.250	1.250	6.000	1.291	1.250	4.7	5.39	CNMG 643
			1 1/2 x 1 1/2	1.820	0	DCRNR/L 24 6D	1.500	1.500	6.000	1.697	1.500	4.7	7.70	CNMG 643

M1 in the end of the ordering code = Modified WF dimension to follow ANSI-standard.

N = Neutral, R = Right hand, L = Left hand

