


T-Max® P cutting unit for turning

Rigid clamp design

Coromant Capto® - Internal coolant supply

KAPR
PSIR

95°
-5°



- CNMM, CNGP
- CNMG
- CNMA, CNGA

					Ordering code	Dimensions, mm, inch							MIID	
			CZC _{MS}	OHX		CNSC	DCON	LF	WF	HF	CP BarPSI			
	12	1/2	C5	105.0	1	C5-DCMNN-00105-12	50	105.0	0.0	0.0	10	3.9	1.09	CNMG 12 04 08
				4.134			1.969	4.134	.000	.000	145	2.394		CNMG 432
			C6	90.0	1	C6-DCMNN-00090-12	63	90.0	0.0	0.0	10	3.9	1.30	CNMG 12 04 08
				3.543			2.480	3.543	.000	.000	145	2.860		CNMG 432
			C6	115.0	1	C6-DCMNN-00115-12	63	115.0	0.0	0.0	10	3.9	1.70	CNMG 12 04 08
				4.528			2.480	4.528	.000	.000	145	3.740		CNMG 432
	16	5/8	C6	90.0	1	C6-DCMNN-00090-16	63	90.0	0.0	0.0	10	6.4	1.30	CNMG 16 06 12
				3.543			2.480	3.543	.000	.000	145	2.860		CNMG 543
			C8	150.0	1	C8-DCMNN-00150-16	80	150.0	0.0	0.0	10	6.4	3.30	CNMG 16 06 12
				5.906			3.150	5.906	.000	.000	145	7.260		CNMG 543

N = Neutral

