






T-Max® insert for turning

Square

Advanced cutting materials



		LE	LE"	ISO CODE	K			S			H	ANSI CODE
					6190	620	650	7925	6060	6065	650	
	09 3/8 8.3 .328	SNGN090312S02520M					☆					SNG323S1020M
	12 1/2 11.5 .453	SNGN120412S02520M					☆					SNG433S1020M
	11.1 .437	SNGN120416S02520M					☆					SNG434S1020M
	12 1/2 11.5 .453	SNGN120412E						☆				SNG433A
	11.5 .453	SNGN120712E						☆				SNG453A
	19 3/4 16.7 .656	SNGN190724E						☆				SNG656A
Finishing 	09 3/8 8.7 .344	SNGN090308T01020				☆			☆	☆	☆	SNG322T0320
	8.3 .328	SNGN090312T01020				☆				☆		SNG323T0320
	12 1/2 11.1 .437	SNGN 12 04 16T01020								☆	☆	SNG434T0320
	11.9 .469	SNGN120408T01020					☆			☆	☆	SNG432T0320
	11.9 .469	SNGN120408T02520					☆			☆	☆	SNG432T0820
	11.5 .453	SNGN120412T01020						☆	☆	☆	☆	SNG433T0320
	11.5 .453	SNGN120412T02520						☆	☆	☆	☆	SNG433T0820
	11.1 .437	SNGN120416T01020							☆			SNG434T0320
	11.1 .437	SNGN120416T02520							☆			SNG434T0820
	11.9 .469	SNGN120708T01020							☆	☆	☆	SNG452T0320
	11.9 .469	SNGN120708T02520							☆	☆	☆	SNG452T0820
	11.5 .453	SNGN120712T01020							☆	☆	☆	SNG453T0320
	11.5 .453	SNGN120712T02520							☆	☆	☆	SNG453T0820
	11.1 .437	SNGN120716K15015							☆			SNG454K6015
	11.1 .437	SNGN120716T01020							☆	☆	☆	SNG454T0320
	11.1 .437	SNGN120716T02520							☆	☆	☆	SNG454T0820
	11.1 .437	SNGN120716T15015							☆			SNG454T6015
	15 5/8 15.1 .594	SNGN150708T01020								☆		SNG552T0320
	14.7 .578	SNGN150712T01020								☆	☆	SNG553T0320
14.3 .562	SNGN150716T01020								☆	☆	SNG554T0320	
14.3 .562	SNGN150716T02520								☆	☆	SNG554T0820	
19 3/4 17.5 .687	SNGN190716T01020								☆		SNG654T0320	
16.7 .656	SNGN190724T01020								☆	☆	SNG656T0320	

For dimensions, see code key on page I14.

