



T-Max® P head for turning

Rigid clamp design

CoroTurn® SL - Internal coolant supply

KAPR 95°
PSIR -5°



- CNMM, CNGP
- CNMG
- CNMA, CNGA

							Dimensions, mm, inch								
		CZC _{MS}	DMIN ₁	OHX	CNSC	Ordering code	DCON	LF	WF	HF	CP BarPSI			MIID	
	12 1/2	32	40.0	38.0	1	570-DCLNR/L-32-12-L	32	38.0	22.0	0.0	10	3.9	0.13	CNMG 12 04 08	
			1.575	1.496			1.260	1.496	.866	.000	145		.286	CNMG 432	
		40		50.0	38.0	1	570-DCLNR/L-40-12-L	40	38.0	27.0	0.0	10	3.9	0.30	CNMG 12 04 08
				1.969	1.496			1.575	1.496	1.063	.000	145		.660	CNMG 432
		16 5/8	40	57.0	40.0	1	570-DCLNR/L-40-16-L	40	40.0	32.0	0.0	10	6.4	0.05	CNMG 16 06 12
				2.244	1.575			1.575	1.575	1.260	.000	145		.110	CNMG 543
		19 3/4	40	57.0	42.0	1	570-DCLNR/L-40-19-L	40	42.0	34.0	0.0	10	6.4	0.05	CNMG 19 06 12
				2.244	1.654			1.575	1.654	1.339	.000	145		.110	CNMG 643

N = Neutral, R = Right hand, L = Left hand

