


T-Max® insert for turning

Rhombic 55°
Advanced cutting materials



						K		S		H	
		LE	LE"	ISO CODE	620	650	650	670	670	ANSI CODE	
Finishing		15	1/2	14.7	.579	DNGN150408T01020	☆	☆	☆	☆	DNG432T0320
				14.3	.563	DNGN150412T01020	☆	☆	☆	☆	DNG433T0320
				13.9	.547	DNGN150416T01020	☆	☆	☆	☆	DNG434T0320
				14.7	.579	DNGN150708T01020	☆	☆	☆	☆	DNG452T0320
				14.3	.563	DNGN150712T01020	☆	☆	☆	☆	DNG453T0320
				14.3	.563	DNGN150712T02520	☆	☆	☆	☆	DNG453T0820
				13.9	.547	DNGN150716K07015	☆	☆	☆	☆	DNG454K3015
				13.9	.547	DNGN150716T01020	☆	☆	☆	☆	DNG454T0320
				13.9	.547	DNGN150716T07015	☆	☆	☆	☆	DNG454T3015

For dimensions, see code key on page I14.

