






CoroCut® 1-2 head for face grooving

Screw clamp design

CoroTurn® SL – Internal coolant supply



									Dimensions, mm, inch									
	SSC	CZC _{MS}	CDX	DAXIN	DAXX	OHX	CNSC	Ordering code	DCON	LF	WF	HF	CP BarPSI	 Nm	 kg	MIID		
	F	32	12.0	40	56.0	12.8	1	570-32R/L123F12B040A	32	14.0	34.4	0.1	10	2.0	0.7	N123F2-0250-0002-CM		
			.472	1.574	2.205	.502			1.260	.551	1.354	.004	145					
		32	12.0	54	70.0	12.8	1	570-32R/L123F12B054A	32	14.0	34.4	0.1	10	2.0	0.7	N123F2-0250-0002-CM		
			.472	2.125	2.756	.502			1.260	.551	1.354	.004	145					
		32	15.0	68	98.0	12.8	1	570-32R/L123F15B068A	32	14.0	37.4	0.1	10	2.0	0.7	N123F2-0250-0002-CM		
			.591	2.677	3.858	.502			1.260	.551	1.472	.004	145					
	G	32	15.0	90	140.0	12.8	1	570-32R/L123F15B090A	32	14.0	37.4	0.1	10	2.0	0.7	N123F2-0250-0002-CM		
			.591	3.543	5.512	.502			1.260	.551	1.472	.004	145					
		32	15.0	130	300.0	12.8	1	570-32R/L123F15B130A	32	14.0	37.4	0.1	10	2.0	0.1	N123F2-0250-0002-CM		
			.591	5.118	11.811	.502			1.260	.551	1.472	.004	145					
		32	12.0	34	44.0	16.5	1	570-32R/L123G12B034A	32	18.0	35.1	0.1	10	2.5	0.7	N123G2-0300-0003-TF		
			.472	1.338	1.732	.650			1.260	.709	1.382	.004	145					
	G	32	15.0	42	60.0	12.5	1	570-32R/L123G15B042A	32	14.0	38.1	0.1	10	3.0	0.7	N123G2-0300-0003-TF		
			.591	1.653	2.362	.492			1.260	.551	1.500	.004	145					
		32	15.0	54	75.0	12.5	1	570-32R/L123G15B054A	32	14.0	38.1	0.1	10	3.0	0.7	N123G2-0300-0003-TF		
			.591	2.125	2.953	.492			1.260	.551	1.500	.004	145					
		32	18.0	67	100.0	12.5	1	570-32R/L123G18B067A	32	14.0	41.1	0.1	10	3.0	0.7	N123G2-0300-0003-TF		
			.709	2.637	3.937	.492			1.260	.551	1.618	.004	145					
	G	32	18.0	90	160.0	12.5	1	570-32R/L123G18B090A	32	14.0	41.1	0.1	10	3.0	0.7	N123G2-0300-0003-TF		
			.709	3.543	6.299	.492			1.260	.551	1.618	.004	145					
		32	18.0	130	300.0	12.5	1	570-32R/L123G18B130A	32	14.0	41.1	0.1	10	3.0	0.7	N123G2-0300-0003-TF		
			.709	5.118	11.811	.492			1.260	.551	1.618	.004	145					
		32	18.0	300	1000.0	14.0	1	570-32R/L123G18B300A	32	14.0	41.1	0.1	10	3.0	0.2	N123G2-0300-0003-TF		
			.709	11.811	39.370	.551			1.260	.551	1.618	.004	145					

SSC = To correspond with SSC on insert.

R = Right hand, L = Left hand

