



# T-Max® insert for turning

Round  
Advanced cutting materials


RCGX..E



RPGN..E



RPGX..E



		ISO CODE	K					S					H	ANSI CODE
			650	6060	6065	650	670	650	6060	6065	650	670		
	06 1/4	RCGX060600T01020	☆											RCGX24T0320
	09 3/8	RCGX090700T01020	☆	☆										RCGX35T0320
		RCGX090700T07015	☆											RCGX35T3015
	12 1/2	RCGX120700K15015	☆											RCGX45K6015
		RCGX120700T01020	☆	☆										RCGX45T0320
		RCGX120700T02520	☆											RCGX45T0820
		RCGX120700T15015	☆											RCGX45T6015
	15 5/8	RCGX151000T20015	☆											RCGX5(6.3)T8015
	19 3/4	RCGX191000K20015	☆											RCGX6(6.3)K8015
		RCGX191000T20015	☆											RCGX6(6.3)T8015
	25 1	RCGX251200K20015	☆										RCGX8(7.6)K8015	
		RCGX251200T20015	☆										RCGX8(7.6)T8015	
	06 1/4	RCGX060600E	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	RCGX24A	
	09 3/8	RCGX090700E	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	RCGX35A	
	12 1/2	RCGX120700E		☆	☆		☆	☆		☆	☆		RCGX45A	
	06 1/4	RPGX060600E		☆									RPGX24A	
	09 3/8	RPGX090700E		☆									RPGX35A	
	12 1/2	RPGX120700E		☆									RPGX45A	
	06 1/4	RPGN060300E		☆									RPG22A	
	09 3/8	RPGN090300E		☆									RPG32A	
	12 1/2	RPGN120400E		☆									RPG43A	
	06 1/4	RPGN060300T01020								☆			RPG22T0320	
	09 3/8	RPGN090300T01020	☆						☆	☆	☆		RPG32T0320	
	12 1/2	RPGN120400T01020								☆			RPG43T0320	
	06 1/4	RPGX060600T01020									☆		RPGX24T0320	
	09 3/8	RPGX090700T01020		☆						☆	☆		RPGX35T0320	
	12 1/2	RPGX120700T01020		☆						☆	☆		RPGX45T0320	

For dimensions, see code key on page I14.

A13   
 A27   
 A558   
 ISO 13399   
 I1