


CoroTurn® 107 insert for turning

Rhombic 80°



		ISO CODE	P										M					K			N		S			ANSI CODE							
			1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	HC15	1125	HC10		HC15	1105	1115	1125	GC15	HC15	
Medium		06 1/4	CCMW 06 02 04																		☆									☆	CCMW 2(1.5)1		
		09 3/8	CCMW 09 T3 04																			☆								☆	CCMW 3(2.5)1		
Medium		06 1/4	CCMT 06 02 08-PR			☆	☆	☆																							CCMT 2(1.5)2-PR		
		09 3/8	CCMT 09 T3 08-PR			☆	☆	☆																								CCMT 3(2.5)2-PR	
			CCMT 09 T3 12-PR			☆	☆	☆																									CCMT 3(2.5)3-PR
		12 1/2	CCMT 12 04 08-PR			☆	☆	☆																									CCMT 432-PR
			CCMT 12 04 12-PR			☆	☆	☆																									CCMT 433-PR
Medium		06 1/4	CCMT 06 02 08-KR																	☆		☆									CCMT 2(1.5)2-KR		
		09 3/8	CCMT 09 T3 08-KR																	☆		☆									CCMT 3(2.5)2-KR		
			CCMT 09 T3 12-KR																		☆		☆									CCMT 3(2.5)3-KR	
		12 1/2	CCMT 12 04 08-KR																		☆		☆									CCMT 432-KR	
			CCMT 12 04 12-KR																		☆		☆									CCMT 433-KR	
Roughing		06 1/4	CCMT 06 02 08-MR								☆		☆																		CCMT 2(1.5)2-MR		
		09 3/8	CCMT 09 T3 08-MR								☆		☆																		CCMT 3(2.5)2-MR		
			CCMT 09 T3 12-MR									☆		☆																		CCMT 3(2.5)3-MR	
		12 1/2	CCMT 12 04 08-MR									☆		☆																		CCMT 432-MR	
			CCMT 12 04 12-MR									☆		☆																		CCMT 433-MR	
Roughing		06 1/4	CCMT 06 02 04-UR				☆	☆						☆																	CCMT 2(1.5)1-UR		
		09 3/8	CCMT 09 T3 04-UR				☆	☆	☆						☆																CCMT 3(2.5)1-UR		
			CCMT 09 T3 08-UR				☆	☆	☆						☆																	CCMT 3(2.5)2-UR	
		12 1/2	CCMT 12 04 08-UR				☆	☆	☆																							CCMT 432-UR	
		16 5/8	CCMT 16 05 08-UR																													CCMT 542-UR	
Roughing		09 3/8	CCMT 09 T3 08-XR												☆												☆			CCMT 3(2.5)2-XR			
			CCMT 09 T3 12-XR													☆											☆			CCMT 3(2.5)3-XR			

For dimensions, see code key on page I14.

A13
 A27
 A558
 I1