


CoroTurn® XS solid-carbide tool for grooving



D	CZC _{MS}	CW	RER	REL	CDX	DMIN ₁	LU	OHX	Ordering code	P M S			Dimensions, mm, inch				
										1025	1025	1025	DCON	LF	WF	WB	
E	4	0.78	0.00	0.00	0.8	4	10.0	13.0	CXS-04G078-4210R	☆	☆	☆	4.0	27.3	2.0	3.0	
		.031	.000	.000	.031	.165	.394	.512	CXS-04G078-4215R/L	☆	☆	☆	.157	1.075	.077	.116	
		0.78	0.00	0.00	0.8	4	15.0	18.0	CXS-04G078-4220R	☆	☆	☆	4.0	32.5	2.0	3.0	
		.031	.000	.000	.031	.165	.591	.709	CXS-04G078-4220R	☆	☆	☆	.157	1.280	.077	.116	
		0.78	0.00	0.00	0.8	4	20.0	23.0	CXS-04G100-4210R/L	☆	☆	☆	4.0	37.6	2.0	3.0	
		.031	.000	.000	.031	.165	.787	.906	CXS-04G100-4210R/L	☆	☆	☆	.157	1.480	.077	.116	
	5	5	0.78	0.00	0.00	1.0	5	10.0	13.0	CXS-04G100-4215R/L	☆	☆	☆	4.0	27.3	2.0	3.0
			.039	.000	.000	.031	.165	.394	.512	CXS-04G100-4215R/L	☆	☆	☆	.157	1.075	.077	.116
			0.78	0.00	0.00	0.8	4	15.0	18.0	CXS-04G100-4220R/L	☆	☆	☆	4.0	32.3	2.0	3.0
			.039	.000	.000	.031	.165	.591	.709	CXS-04G100-4220R/L	☆	☆	☆	.157	1.272	.077	.116
			0.78	0.00	0.00	0.8	4	20.0	23.0	CXS-04G100-4220R/L	☆	☆	☆	4.0	37.3	2.0	3.0
			.039	.000	.000	.031	.165	.787	.906	CXS-04G100-4220R/L	☆	☆	☆	.157	1.469	.077	.116
F	5	0.78	0.00	0.00	1.0	5	10.0	13.0	CXS-05G078-5210R	☆	☆	☆	5.0	32.4	2.5	3.8	
		.031	.000	.000	.039	.204	.394	.512	CXS-05G078-5210R	☆	☆	☆	.197	1.276	.096	.148	
		0.78	0.00	0.00	1.0	5	20.0	23.0	CXS-05G078-5220R/L	☆	☆	☆	5.0	42.5	2.5	3.8	
		.031	.000	.000	.039	.204	.787	.906	CXS-05G078-5220R/L	☆	☆	☆	.197	1.673	.096	.148	
		0.78	0.00	0.00	1.0	5	30.0	33.0	CXS-05G078-5230R	☆	☆	☆	5.0	52.7	2.5	3.8	
		.031	.000	.000	.039	.204	1.181	1.299	CXS-05G078-5230R	☆	☆	☆	.197	2.075	.096	.148	
	5	5	1.00	0.00	0.00	1.0	5	10.0	13.0	CXS-05G100-5210R	☆	☆	☆	5.0	32.3	2.5	3.8
			.039	.000	.000	.039	.204	.394	.512	CXS-05G100-5210R	☆	☆	☆	.197	1.272	.096	.148
			1.00	0.00	0.00	1.0	5	20.0	23.0	CXS-05G100-5220R/L	☆	☆	☆	5.0	42.3	2.5	3.8
			.039	.000	.000	.039	.204	.787	.906	CXS-05G100-5220R/L	☆	☆	☆	.197	1.665	.096	.148
			1.00	0.00	0.00	1.0	5	30.0	33.0	CXS-05G100-5230R	☆	☆	☆	5.0	52.3	2.5	3.8
			.039	.000	.000	.039	.204	1.181	1.299	CXS-05G100-5230R	☆	☆	☆	.197	2.059	.096	.148
5	5	1.17	0.00	0.00	1.0	5	10.0	13.0	CXS-05G117-5210R	☆	☆	☆	5.0	32.4	2.5	3.8	
		.046	.000	.000	.039	.204	.394	.512	CXS-05G117-5210R	☆	☆	☆	.197	1.276	.096	.148	
		1.17	0.00	0.00	1.0	5	20.0	23.0	CXS-05G117-5220R/L	☆	☆	☆	5.0	42.5	2.5	3.8	
		.046	.000	.000	.039	.204	.787	.906	CXS-05G117-5220R/L	☆	☆	☆	.197	1.673	.096	.148	
		1.17	0.00	0.00	1.0	5	30.0	33.0	CXS-05G117-5230R	☆	☆	☆	5.0	52.7	2.5	3.8	
		.046	.000	.000	.039	.204	1.181	1.299	CXS-05G117-5230R	☆	☆	☆	.197	2.075	.096	.148	
5	5	1.50	0.00	0.00	1.0	5	10.0	13.0	CXS-05G150-5210R	☆	☆	☆	5.0	32.3	2.5	3.8	
		.059	.000	.000	.039	.204	.394	.512	CXS-05G150-5210R	☆	☆	☆	.197	1.272	.096	.148	
		1.50	0.00	0.00	1.0	5	15.0	18.0	CXS-05G150-5215R/L	☆	☆	☆	5.0	37.3	2.5	3.8	
		.059	.000	.000	.039	.204	.591	.709	CXS-05G150-5215R/L	☆	☆	☆	.197	1.469	.096	.148	
		1.50	0.00	0.00	1.0	5	20.0	23.0	CXS-05G150-5220R/L	☆	☆	☆	5.0	42.3	2.5	3.8	
		.059	.000	.000	.039	.204	.787	.906	CXS-05G150-5220R/L	☆	☆	☆	.197	1.665	.096	.148	
5	5	1.50	0.00	0.00	1.0	5	30.0	33.0	CXS-05G150-5230R	☆	☆	☆	5.0	52.3	2.5	3.8	
		.059	.000	.000	.039	.204	1.181	1.299	CXS-05G150-5230R	☆	☆	☆	.197	2.059	.096	.148	
		1.57	0.00	0.00	1.0	5	10.0	13.0	CXS-05G157-5210R	☆	☆	☆	5.0	32.4	2.5	3.8	
		.062	.000	.000	.039	.204	.394	.512	CXS-05G157-5210R	☆	☆	☆	.197	1.276	.096	.148	

CZC MS to correspond with CZC WS on holder R = Right hand, L = Left hand

Tolerances:

CXS-xxG	CWTOLL	CWTOLU	CWTOLL"	CWTOLU"	RETOLL	RETOLU	RETOLL"	RETOLU"
CXS-xxG	0.00	0.05	.0000	.0020	0.00	0.02	.0000	.0008

G2
 B172
 GC
 B192
 ISO 13399
 I1
 C3-DC
 I19

