


CoroTurn® 107 insert for turning

Rhombic 55°



	ISO CODE	P										M					K			N		S			ANSI CODE							
		1515	1525	4205	4235	4315	4325	5015	GC30	1115	1125	2015	2025	2035	235	GC15	3005	3205	3210	3215	GC30	HI3A	1125	HI10		HI3A	1105	1115	1125	GC15	HI3A	SBF
Medium	11 3/8 DCMW 11 T3 04																															DCMW 3(2.5)1
	11 3/8 DCMT 11 T3 08-PR DCMT 11 T3 12-PR			☆	☆	☆	☆																									DCMT 3(2.5)2-PR DCMT 3(2.5)3-PR
Roughing	11 3/8 DCMT 11 T3 08-KR DCMT 11 T3 12-KR																☆	☆	☆	☆											DCMT 3(2.5)2-KR DCMT 3(2.5)3-KR	
	11 3/8 DCMT 11 T3 08-MR DCMT 11 T3 12-MR										☆	☆	☆																		DCMT 3(2.5)2-MR DCMT 3(2.5)3-MR	
	11 3/8 DCMT 11 T3 04-UR DCMT 11 T3 08-UR DCMT 11 T3 12-UR				☆	☆	☆					☆	☆																		DCMT 3(2.5)1-UR DCMT 3(2.5)2-UR DCMT 3(2.5)3-UR	
	11 3/8 DCMT 11 T3 08-XR DCMT 11 T3 12-XR							☆							☆					☆								☆			DCMT 3(2.5)2-XR DCMT 3(2.5)3-XR	

For dimensions, see code key on page I14.

A13
 A27
 A558
 ISO 13399
 I1