

# メートルねじの呼寸とピッチ

## Metric limit thread gauge of nominal diameter and pitch

ねじの呼び	並目ピッチ	細目ピッチ					ねじの呼び	並目ピッチ	細目ピッチ				
M1	0.25	0.2				M52	☆5	☆4	☆3	2	1.5		
M1.1	☆0.25	☆0.2				M55		☆4	☆3	2	1.5		
M1.2	0.25	0.2				M56	☆5.5	☆4	☆3	☆2	☆1.5		
M1.4	0.3	0.2				M58		☆4	☆3	2	1.5		
M1.6	☆0.35	☆0.2				M60	☆5.5	☆4	☆3	2	1.5		
M1.7	◎0.35	●0.2				M62		☆4	☆3	2	1.5		
M1.8	☆0.35	☆0.2				M64	☆6	☆4	☆3	☆2	☆1.5		
M2	0.4	0.25				M65		☆4	☆3	2	1.5		
M2.2	☆0.45	☆0.25				M68	☆6	☆4	☆3	2	1.5		
M2.3	◎0.4	●0.25				M70		☆6	☆4	☆3	2	1.5	
M2.5	☆0.45	☆0.35				M72		☆6	☆4	☆3	2	1.5	
M2.6	◎0.45	●0.35				M75			☆4	☆3	2	1.5	
M3	☆0.5					M76		☆6	☆4	☆3	☆2	☆1.5	
M3	●0.6	0.35				M78					2	●1.5	
M3.5	0.6	0.35				M80		☆6	☆4	☆3	2	1.5	
M4	☆0.7					M82					2	●1.5	
M4	●0.75	0.5				M85		☆6	☆4	☆3	2	●1.5	
M4.5	0.75	0.5				M88					●2	●1.5	
M5	☆0.8					M90		☆6	☆4	☆3	2	●1.5	
M5	●0.9	0.5				M92					●2	●1.5	
M5.5	●0.9	0.5				M95		☆6	☆4	☆3	2	●1.5	
M6	1	0.75	●0.5			M98					●2	●1.5	
M7	1	0.75	●0.5			M100		☆6	☆4	☆3	2	●1.5	
M8	1.25	1	0.75	●0.5		M102					●2	●1.5	
M9	1.25	1	0.75	●0.5		M105		☆6	☆4	☆3	2	●1.5	
M10	1.5	1.25	1	☆0.75	●0.5	M108					●2	●1.5	
M11	☆1.5	●1.25	1	☆0.75	●0.5	M110		☆6	☆4	☆3	2	●1.5	
M12	1.75	1.5	☆1.25	1	●0.5	M112					●2	●1.5	
M13		●1.5		●1	●0.5	M115		☆6	☆4	☆3	2	●1.5	
M14	2	1.5	☆1.25	1	●0.5	M118					●2	●1.5	
M15		1.5		1	●0.5	M120		☆6	☆4	☆3	2	●1.5	
M16	2	1.5		1	●0.5	M122					●2		
M17		☆1.5		☆1		M125		☆6	☆4	☆3	2		
M18	2.5	2	1.5	1	●0.5	M128					●2		
M20	2.5	2	1.5	1	●0.5	M130		☆6	☆4	☆3	2		
M22	2.5	2	1.5	1	●0.5	M132					●2		
M24	3	2	1.5	1	●0.5	M135		☆6	☆4	☆3	2		
M25		2	1.5	1	●0.5	M138					●2		
M26		●2	1.5	●1	●0.5	M140		☆6	☆4	☆3	2		
M27	3	☆2	1.5	☆1		M142					●2		
M28		2	1.5	1	●0.5	M145		☆6	☆4	☆3	2		
M30	3.5	☆3	2	1.5	1	●0.5	M148				●2		
M32			2	1.5	●1	●0.5	M150		☆6	☆4	☆3	2	
M33	3.5	☆3	☆2	1.5		M155		☆6	☆4	☆3			
M34			●2	●1.5	●1	●0.5	M160		☆6	☆4	☆3		
M35				1.5		M165		☆6	☆4	☆3			
M36	4	☆3	2	1.5	●1	●0.5	M170		☆6	☆4	☆3		
M38			●2	1.5	●1	●0.5	M175		☆6	☆4	☆3		
M39	4	☆3	☆2	☆1.5		M180		☆6	☆4	☆3			
M40		☆3	2	1.5	●1	M185		☆6	☆4	☆3			
M42	4.5	☆4	☆3	2	1.5	●1	M190		☆6	☆4	☆3		
M45	4.5	☆4	☆3	2	1.5	●1	M195		☆6	☆4	☆3		
M48	5	☆4	☆3	2	1.5	●1	M200		☆6	☆4	☆3		
M50			☆3	2	1.5	●1							

(注) ☆：ISOより採用されたもの ●：1968年3月限りで廃止されたもの（旧JIS） ◎：1977年にJISより廃止予定のもの