



CoroTurn® 107 head for turning

Screw clamp design

CoroTurn® SL - Internal coolant supply

KAPR
PSIR

95°
-5°



- CCMT, CCGT
CCGX, CCET
- CCMW

							Dimensions, mm, inch							MIID	
			CZC _{MS}	DMIN ₁	OHX	CNSC	Ordering code	DCON	LF	WF	HF	CP BarPSI			
	06	1/4	16	20.0	20.0	1	570-SCLCR/L-16-06	16	20.0	11.0	0.0	10	0.9	0.03	CCMT 06 02 04
				.787	.787			.630	.787	.433	.000	145		.062	CCMT 2(1.5)1
	09	3/8	20	25.0	20.0	1	570-SCLCR/L-20-09	20	20.0	13.0	0.0	10	3.0	0.05	CCMT 09 T3 08
				.984	.787			.787	.787	.512	.000	145		.103	CCMT 3(2.5)2
			25	32.0	20.0	1	570-SCLCR/L-25-09	25	20.0	17.0	0.0	10	3.0	0.08	CCMT 09 T3 08
				1.260	.787			.984	.787	.669	.000	145		.183	CCMT 3(2.5)2
		32	40.0	32.0	1	570-SCLCR/L-32-09	32	32.0	22.0	0.0	10	3.0	0.12	CCMT 09 T3 08	
			1.575	1.260			1.260	1.260	.866	.000	145		.264	CCMT 3(2.5)2	
	12	1/2	40	50.0	38.0	1	570-SCLCR/L-40-12	40	38.0	27.0	0.0	10	3.0	0.19	CCMT 12 04 08
				1.969	1.496			1.575	1.496	1.063	.000	145		.407	CCMT 432

N = Neutral, R = Right hand, L = Left hand

