

# Silent Smooth Castors III

—Stainless steel twin wheeled compact heavy duty type—

RoHS compliant products.


## POINT

- Bearings and bracket (including balls in swivel head) are made of **stainless steel. (SUS304)**
- Thanks to **combination of thrust bearing and ball bearing** in the swivel head, it **moves lightly and turns easily** even with a heavy load.
- Electrically conductive nylon as one of possible countermeasures against static electricity/ MCD.
- **Rotates smoothly** after a long-term fixation under a heavy load.

## USE EXAMPLE

- For fixed precision machines to be occasionally relocated in a workplace, or moved as production line is rearranged.
  - For heavy duty slow-moving carriers.
- ©We'll accept your custom-order. Please feel free to contact us.  
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
- ©Please feel free to ask about the product weight for each item.

**Starting resistance to a right angle is down compared to a single wheeled castor!**



## SUHJTS Swivel castors

SUHJTS-50


SUHJTS-65

SUHJTS-75


## WHEELS ··· Stainless steel radial ball bearing

See P.62 to P.71 for detailed description.



MC (Monomer cast nylon/Blue) 



MCMO (Monomer cast nylon/Black) 



MCD (Conductive monomer cast nylon/Black) 

• Volume resistance  $10^2 \sim 10^4 \Omega \cdot \text{cm}^*$   
\*For reference only, not guaranteed.