

Electrically Conductive Castors II – Medium duty type (Stainless steel) –


RoHS compliant products.

POINT

- Wheel center, bracket (including balls in swivel head) and bearings are made of **stainless steel. (SUS304)**
- Wheels are made of homogeneous electrically conductive material. Long lasting performance even after friction.
- SEUW wheel: **Carbonless materials** result in non-marking.
- **Electrically conductive grease** in the swivel head.
- Smooth swiveling thanks to **double bearing** in the swivel head with dust shield for balls.
- SEUW wheel comes with **box style structure**.

USE EXAMPLE

- For electric parts carriers and precise measuring equipment.
 - For carriers in clean room.
- ©We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
©Please feel free to ask about the product weight for each item.



SUNJ Swivel castors



SUNJ-75 (available with MCD)

SUNJ-100

SUNJ-125

SUNJ-150

SUNJ-200 (available with MCD. Upon request)

SUNJB Swivel with stopper



SUNJB-100

SUNJB-125

SUNJB-150

SUNK Fixed castors



SUNK-75 (available with MCD)

SUNK-100

SUNK-125

SUNK-150

SUNK-200 (available with MCD. Upon request)

WHEELS NBS ...Stainless steel needle bearing

See P.62 to P.71 for detailed description.



SEUW (Antistatic UR) NBS

• Volume resistance $10^6 \sim 10^9 \Omega \cdot \text{cm}^*$

MCD NBS

(Conductive monomer cast nylon)

• Volume resistance $10^2 \sim 10^4 \Omega \cdot \text{cm}^*$

NB with stopper type: not available.

*For reference only, not guaranteed.