



# CoroCut® 1-2 head for profiling

Screw clamp design

CoroTurn® SL – High precision coolant supply



SSC	CZC <sub>MS</sub>	CDX <sub>1</sub>	CDX <sub>2</sub>	DMIN <sub>1</sub>	DAXN	OHX	CNSC	Ordering code	Dimensions, mm, inch						MIID	
									LF	WF	WSC	CP BarPSI	Nm	Kg		
	G	70	15.0	15.0	100.0	800.0	14.0	1	SL70-R/L123G15A-HP	15.5	48.0	70.0	80	4.0	0.23	N123G2-0300-GM
			.591	.591	3.937	31.496	.551			.610	1.890	2.756	1160			
	H	70	30.0	30.0	100.0	800.0	14.0	1	SL70-R/L123H30A-HP	16.0	56.0	70.0	80	4.5	0.25	N123H2-0400-GM
			1.181	1.181	3.937	31.496	.551			.630	2.205	2.756	1160			
	J	70	15.0	15.0	120.0	320.0	15.0	1	SL70-R/L123K15A-HP	18.0	36.0	70.0	80	2.0	0.25	N123J2-0600-RO
			.591	.591	4.724	12.598	.591			.709	1.417	2.756	1160			
	K	70	45.0	45.0	120.0	320.0	15.0	1	SL70-R/L123K45A-HP	18.0	71.0	70.0	80	6.0	0.30	N123K2-0600-GM
			1.772	1.772	4.724	12.598	.591			.709	2.795	2.756	1160			
	L	70	50.0	50.0	105.0	340.0	14.0	1	SL70-R/L123L50A-HP	18.0	81.0	70.0	80	6.5	0.34	N123L2-0800-RO
			1.969	1.969	4.134	13.386	.551			.709	3.189	2.756	1160			
M	70	50.0	50.0	100.0	450.0	12.0	1	SL70-R/L123M50A-HP	17.5	71.0	70.0	80	5.0	0.35	N123M1-1100-0008-GM	
		1.969	1.969	3.937	17.717	.472			.689	2.795	2.756	1160				
R	70	65.0	65.0	125.0	500.0	9.0	1	SL70-R/L123R65A-HP	16.5	71.0	70.0	80	6.5	0.34	N123R1-1500-0010-GR	
		2.559	2.559	4.921	19.685	.354			.650	2.795	2.756	1160				
K	70	30.0	30.0	120.0	320.0	14.0	1	SL70-R/L123K30A-HP-M	17.0	55.0	70.0	80	4.5	0.27	N123K2-0600-GM	
		1.181	1.181	4.724	12.598	.551			.669	2.165	2.756	1160				
L	70	35.0	35.0	90.0	270.0	14.0	1	SL70-R/L123L35A-HP-M	18.0	61.0	70.0	80	6.5	0.28	N123L2-0800-RO	
		1.378	1.378	3.543	10.630	.551			.709	2.402	2.756	1160				

SSC = To correspond with SSC on insert.

R = Right hand, L = Left hand

