




- Material : Plated steel, Stainless Steel
- 材質 : SS(三価クロメートメッキ)・SUS304

## ストレートタイプアダプター

### SR-06 (同径)


※印のSUS304は32



接続口金具 : SR-02

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEX <sub>1</sub> mm		HEX <sub>2</sub> mm
							SUS	SS	
3	G 1/8	R 1/8	10	6	3.0	31	14		14
6	G 1/4	R 1/4	13	8	5.5	38	19		19
9	G 3/8	R 3/8	15	8	7.0	42	22		22
12	G 1/2	R 1/2	18	10	10.0	50	27		27
19	G 3/4	R 3/4	20	12	16.0	56	32	36	※36
25	G 1	R 1	22	12	22.0	60	38	41	41
32	G 1 1/4	R 1 1/4	25	14	28.0	69	46	50	50
38	G 1 1/2	R 1 1/2	25	14	34.0	72	50	60	60
50	G 2	R 2	30	17	45.0	83	63	70	70

### SR-06 (異径)




接続口金具 : SR-02

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	d <sub>1</sub> φmm	d <sub>2</sub> φmm	Lmm	H1	H2
6×9	G 1/4	R 3/8	15	8	5.5	7.0	40	19	19
9×12	G 3/8	R 1/2	18	10	7.0	10.0	47	22	22
12×19	G 1/2	R 3/4	20	12	10.0	16.0	54	27	27
19×25	G 3/4	R 1	22	12	16.0	22.0	58	36	36
* 25×32	G 1	R 1 1/4	25	14	22.0	28.0	65	41	50
* 32×38	G 1 1/4	R 1 1/2	25	14	28.0	34.0	68	50	60
* 38×50	G 1 1/2	R 2	30	14	34.0	45.0	76	60	70

### SR-06 (異径)



接続口金具 : SR-02

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	d <sub>1</sub> φmm	d <sub>2</sub> φmm	Lmm	H1	H2
6×3	G 1/4	R 1/8	10	8	5.5	4.0	35	19	19
9×6	G 3/8	R 1/4	13	8	7.0	5.5	40	22	22
12×9	G 1/2	R 3/8	15	8	10.0	7.0	45	27	27
19×12	G 3/4	R 1/2	18	10	16.0	10.0	52	36	32
25×19	G 1	R 3/4	20	12	22.0	16.0	58	41	38
* 32×25	G 1 1/4	R 1	22	12	28.0	22.0	63	50	41
* 38×32	G 1 1/2	R 1 1/4	25	14	34.0	28.0	71	60	50
* 50×38	G 2	R 1 1/2	25	17	45.0	34.0	77	70	60