




SERスクレーパ



SERスクレーパ寸法表

単位：mm

呼び番号		スクレーパおよびみぞ寸法						
標準 (RN 906)	耐熱用 (RF 905)	d	D	H	t	G	C	B
SER- 3		3	6	2.75	2	2.5	4.5	1.5
SER- 4		4	7	2.75	2	2.5	5.5	1.5
SER- 5		5	8	2.75	2	2.5	6.5	1.5
SER- 6		6	9	2.75	2	2.5	7.5	1.5
SER- 7		7	10	2.75	2	2.5	8.5	1.5
SER- 8	SER- 8F	8	11	2.75	2	2.5	9.5	1.5
SER- 9	SER- 9F	9	12	2.75	2	2.5	10.5	1.5
SER- 10		10	13	2.75	2	2.5	11.5	1.5
SER- 10A	SER- 10AF	10	14	3.9	2.9	3.2	12	1.5
SER- 11.2		11.2	15.2	3.9	2.9	3.2	13.2	1.5
SER- 12	SER- 12F	12	16	3.9	2.9	3.2	14	1.5
SER- 12.5		12.5	16.5	3.9	2.9	3.2	14.5	1.5
SER- 14	SER- 14F	14	18	3.9	2.9	3.2	16	1.5
SER- 15		15	19	3.9	2.9	3.2	17	1.5
SER- 16	SER- 16F	16	20	3.9	2.9	3.2	18	1.5
SER- 18	SER- 18F	18	22	3.9	2.9	3.2	20	1.5
SER- 20	SER- 20F	20	24	3.9	2.9	3.2	22	1.5
SER- 22		22	26	3.9	2.9	3.2	24	1.5
SER- 22A		22	28	5.8	4.3	4.7	25	2
SER- 22.4		22.4	28.4	5.8	4.3	4.7	25.4	2
SER- 24		24	30	5.8	4.3	4.7	27	2
SER- 25	SER- 25F	25	31	5.8	4.3	4.7	28	2
SER- 26		26	32	5.8	4.3	4.7	29	2
SER- 28		28	34	5.8	4.3	4.7	31	2
SER- 30	SER- 30F	30	36	5.8	4.3	4.7	33	2
SER- 32		32	38	5.8	4.3	4.7	35	2
SER- 34		34	40	5.8	4.3	4.7	37	2
SER- 35	SER- 35F	35	41	5.8	4.3	4.7	38	2
SER- 35.5	SER- 35.5F	35.5	41.5	5.8	4.3	4.7	38.5	2
SER- 36		36	42	5.8	4.3	4.7	39	2
SER- 38		38	44	5.8	4.3	4.7	41	2
SER- 40	SER- 40F	40	46	5.8	4.3	4.7	43	2
SER- 42		42	48	5.8	4.3	4.7	45	2
SER- 44		44	50	5.8	4.3	4.7	47	2
SER- 45		45	51	5.8	4.3	4.7	48	2
SER- 46		46	52	5.8	4.3	4.7	49	2
SER- 48		48	54	5.8	4.3	4.7	51	2
SER- 50		50	56	5.8	4.3	4.7	53	2
SER- 50A		50	58	9.4	6.9	7.5	55	3
SER- 55		55	65	9.4	6.9	7.5	60	3
SER- 56		56	66	9.4	6.9	7.5	61	3
SER- 58		58	68	9.4	6.9	7.5	63	3
SER- 60		60	70	9.4	6.9	7.5	65	3
SER- 65		65	75	9.4	6.9	7.5	70	3
SER- 70		70	80	9.4	6.9	7.5	75	3
SER- 71		71	81	9.4	6.9	7.5	76	3
SER- 75		75	85	9.4	6.9	7.5	80	3
SER- 80		80	90	9.4	6.9	7.5	85	3
SER- 85		85	95	9.4	6.9	7.5	90	3
SER- 90	SER- 90F	90	100	9.4	6.9	7.5	95	3
SER- 95		95	105	9.4	6.9	7.5	100	3
SER- 100		100	110	9.4	6.9	7.5	105	3

★ご注文・お問合せは、呼び番号にてご指示下さい。 ★表中 呼び番号が色地のものは、在庫しております。