


ストレートタイプアダプター

- Material : Plated steel, Stainless Steel
- 材質 : SS(三価クロメートメッキ)・SUS304

SR-07 (同径)





接続口金具 : SR-01・SR-05

※印のSUS304は32

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	dφmm	Lmm	HEXmm
3	G 1/8	Rc 1/8	15	11	3.0	26	14
6	G 1/4	Rc 1/4	17	13	5.5	30	19
9	G 3/8	Rc 3/8	19	15	7.0	34	22
12	G 1/2	Rc 1/2	22	18	10.0	40	27
19	G 3/4	Rc 3/4	25	20	16.0	45	※36
25	G 1	Rc 1	27	22	22.0	49	41
32	G 1 1/4	Rc 1 1/4	30	24	28.0	54	50
38	G 1 1/2	Rc 1 1/2	30	24	34.0	54	60
50	G 2	Rc 2	36	28	45.0	64	70
65	G 2 1/2	Rc 2 1/2	42	33	56.0	75	90

SR-07 (異径)




接続口金具 : SR-01・SR-05

*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	dφmm	Lmm	HEXmm
3×6	G 1/8	Rc 1/4	17	11	4.0	28	19
6×9	G 1/4	Rc 3/8	19	13	5.5	32	22
9×12	G 3/8	Rc 1/2	22	15	7.0	37	27
12×19	G 1/2	Rc 3/4	25	18	10.0	43	36
19×25	G 3/4	Rc 1	27	20	16.0	47	41
* 25×32	G 1	Rc 1 1/4	30	22	22.0	52	50
* 32×38	G 1 1/4	Rc 1 1/2	30	24	28.0	54	60
* 38×50	G 1 1/2	Rc 2	36	24	34.0	60	70

SR-07 (異径)



接続口金具 : SR-01・SR-05

*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	dφmm	Lmm	HEXmm
6×3	G 1/4	Rc 1/8	14	13	5.5	27	19
9×6	G 3/8	Rc 1/4	17	15	7.0	32	22
12×9	G 1/2	Rc 3/8	19	18	10.0	37	27
19×12	G 3/4	Rc 1/2	22	20	16.0	42	32
25×19	G 1	Rc 3/4	27	22	22.0	49	36
* 32×25	G 1 1/4	Rc 1	27	24	28.0	51	50
* 38×32	G 1 1/2	Rc 1 1/4	30	24	34.0	54	50
* 50×38	G 2	Rc 1 1/2	30	28	45.0	58	60