


フィメールコネクター (ストレートネジタイプ)

FEMALE CONNECTOR (SPW Type)



UNIT : mm

型番	チューブ外径	管用平行ネジ	最小孔径	差込深さ	組込長さ	本体長さ	六角対辺		ねじ深さ
TYPE NO.	TUBE O.D.	PIPE THREAD	MIN. BORE	DEPTH	APPROX	BODY	WIDTH ACROSS HEX		DEPTH
	T	P	A	B	C	D	E	F	H

[ミリサイズチューブ用]

SPW- 6M- 2GC	6	G1/8	3	15.6	32.1	24.5	15.8	14	9
SPW- 6M- 4GC	6	G1/4	4.5	15.6	36.1	28.5	19	14	14
SPW- 6M- 6GC	6	G3/8	4.5	15.6	38.1	30.5	22	14	16
SPW- 6M- 8GC	6	G1/2	4.5	15.6	43.1	35.5	27	14	17.5
SPW- 8M- 2GC	8	G1/8	3	16.4	32.7	25	15.8	15.8	9
SPW- 8M- 4GC	8	G1/4	5.5	16.4	36.7	29	19	15.8	14
SPW- 8M- 6GC	8	G3/8	5.5	16.4	38.7	31	22	15.8	16
SPW- 8M- 8GC	8	G1/2	5.5	16.4	43.7	36	27	15.8	17.5
SPW-10M- 2GC	10	G1/8	3	17.2	33.7	26	19	19	9
SPW-10M- 4GC	10	G1/4	5.5	17.2	37.7	30	19	19	14
SPW-10M- 6GC	10	G3/8	5.5	17.2	39.7	32	22	19	16
SPW-10M- 8GC	10	G1/2	5.5	17.2	44.7	37	27	19	17.5
SPW-12M- 2GC	12	G1/8	3	23.1	37.4	27	22	22	9
SPW-12M- 4GC	12	G1/4	5.5	23.1	40.4	30	22	22	14
SPW-12M- 6GC	12	G3/8	5.5	23.1	42.4	32	22	22	16
SPW-12M- 8GC	12	G1/2	5.5	23.1	47.4	37	27	22	17.5

[インチサイズチューブ用] チューブ外径の () 内はインチ表示

SPW- 4C- 2GC	6.35(1/4")	G1/8	3	15.6	32.1	24.5	15.8	14	9
SPW- 4C- 4GC	6.35(1/4")	G1/4	4.8	15.6	36.1	28.5	19	14	14
SPW- 4C- 6GC	6.35(1/4")	G3/8	4.8	15.6	38.1	30.5	22	14	16
SPW- 4C- 8GC	6.35(1/4")	G1/2	4.8	15.6	43.1	35.5	27	14	17.5
SPW- 6C- 2GC	9.52(3/8")	G1/8	3	17.2	33.7	26	19	17.4	9
SPW- 6C- 4GC	9.52(3/8")	G1/4	5.5	17.2	37.7	30	19	17.4	14
SPW- 6C- 6GC	9.52(3/8")	G3/8	5.5	17.2	39.7	32	22	17.4	16
SPW- 6C- 8GC	9.52(3/8")	G1/2	5.5	17.2	44.7	37	27	17.4	17.5
SPW- 8C- 2GC	12.7(1/2")	G1/8	3	23.1	37.4	27	22	22	9
SPW- 8C- 4GC	12.7(1/2")	G1/4	5.5	23.1	40.4	30	22	22	14
SPW- 8C- 6GC	12.7(1/2")	G3/8	5.5	23.1	42.4	32	22	22	16
SPW- 8C- 8GC	12.7(1/2")	G1/2	5.5	23.1	47.4	37	27	22	17.5

[鋼管サイズパイプ用] チューブ外径の () 内は鋼管サイズ表示

SPW- 6A- 2GC	10.5(6A)	G1/8	3.0	17.4	33.3	25.4	19.0	22.0	9.0
SPW- 6A- 4GC	10.5(6A)	G1/4	5.5	17.4	38.1	30.2	19.0	22.0	14.0
SPW- 6A- 6GC	10.5(6A)	G3/8	5.5	17.4	39.6	31.4	22.0	22.0	16.0
SPW- 6A- 8GC	10.5(6A)	G1/2	5.5	17.4	44.4	36.5	27.0	22.0	17.5
SPW- 8A- 4GC	13.8(8A)	G1/4	5.5	23.3	40.8	30.2	22.0	24.0	14.0
SPW- 8A- 6GC	13.8(8A)	G3/8	5.5	23.3	42.3	31.7	22.0	24.0	16.0
SPW- 8A- 8GC	13.8(8A)	G1/2	5.5	23.3	47.1	36.5	27.0	24.0	17.5
SPW-10A- 8GC	17.3(10A)	G1/2	5.5	24.9	47.1	36.5	27.0	30.0	17.5
SPW-15A- 8GC	21.7(15A)	G1/2	5.5	26.6	49.1	38.5	30.0	32.0	17.5

◎A寸法はチューブ側とねじ側 (P側) で異なる場合があります。

◎製品改良のため、形状及び寸法は、予告無く変更することがありますので、あらかじめご了承下さい。