


ストレートタイプアダプター

● Material : Plated steel, Stainless Steel
● 材質 : SS(三価クロメートメッキ)・SUS304


SR-09 (同径)



接続口金具 : SR-05

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm	
								SUS	SS
3	G 1/8	R 1/8	10	6	11	4.0	27	14	
6	G 1/4	R 1/4	13	8	13	5.5	34	19	
9	G 3/8	R 3/8	15	8	15	7.0	38	22	
12	G 1/2	R 1/2	18	10	18	10.0	46	27	
19	G 3/4	R 3/4	20	12	20	16.0	52	32	36
25	G 1	R 1	22	12	22	22.0	56	38	41
32	G 1 1/4	R 1 1/4	25	14	24	28.0	63	46	50
38	G 1 1/2	R 1 1/2	25	14	24	34.0	63	50	60
50	G 2	R 2	30	17	28	45.0	75	63	70
65	G 2 1/2	R 2 1/2	33	17	33	56.0	83	80	
75	G 3	R 3	38	18	34	68.0	90	90	
100	G 4	R 4	45	22	45	88.0	112	120	

SR-09 (異径)




接続口金具 : SR-05

*印のSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ φmm	d ₂ φmm	Lmm	HEXmm
3×6	G 1/8	R 1/4	13	8	11	4.0	5.5	32	14
6×9	G 1/4	R 3/8	15	8	13	5.5	7.0	36	19
9×12	G 3/8	R 1/2	18	10	15	7.0	10.0	43	22
12×19	G 1/2	R 3/4	20	10	18	10.0	16.0	48	27
19×25	G 3/4	R 1	22	12	20	16.0	22.0	54	36
* 25×32	G 1	R 1 1/4	25	14	22	22.0	28.0	61	46
* 32×38	G 1 1/4	R 1 1/2	25	14	24	28.0	28.0	63	50
* 38×50	G 1 1/2	R 2	30	14	24	33.0	33.0	68	60

SR-09 (異径)



接続口金具 : SR-05

*印のSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ φmm	d ₂ φmm	Lmm	HEXmm
6×3	G 1/4	R 1/8	10	8	13	5.5	4.0	31	19
9×6	G 3/8	R 1/4	13	8	15	7.0	5.5	36	22
12×9	G 1/2	R 3/8	15	10	18	10.0	7.0	43	27
19×12	G 3/4	R 1/2	18	12	20	16.0	10.0	50	32
25×19	G 1	R 3/4	20	12	22	22.0	16.0	54	38
* 32×25	G 1 1/4	R 1	22	14	24	28.0	22.0	60	46
* 38×32	G 1 1/2	R 1 1/4	25	14	24	28.0	28.0	63	50
* 50×38	G 2	R 1 1/2	25	14	28	33.0	33.0	67	60

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。