


エルボータイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)


UL-45 (06)



\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	dφmm	Emm	HEXmm
6	G ¼	R ¼	24	19	13	5.5	17	19
9	G ⅜	R ⅜	27	22	15	7.0	19	22
12	G ½	R ½	34	26	18	10.0	24	27
19	G ¾	R ¾	41	30	20	16.0	30	36
25	G 1	R 1	46	34	22	22.0	36	41
* 32	G 1¼	R 1¼	53	38	24	28.0	45	50
* 38	G 1½	R 1½	58	40	24	34.0	50	60
* 50	G 2	R 2	64	48	28	45.0	63	70

UL-45 (0609)




\*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	Emm	HEXmm
6	G ¼	24	19	13	5.5	17	19
9	G ⅜	27	22	15	7.0	19	22
12	G ½	34	26	18	10.0	24	27
19	G ¾	41	30	20	16.0	30	36
25	G 1	46	34	22	22.0	36	41
* 32	G 1¼	53	38	24	28.0	45	50
* 38	G 1½	58	40	24	34.0	50	60
* 50	G 2	64	48	28	45.0	63	70

接続口金具 : SR-02・SR-05

UL-45 (0613)



\*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	Emm	HEXmm
6	G ¼	24	22.0	16.0	5.5	17	19
9	G ⅜	27	24.5	17.5	7.0	19	22
12	G ½	34	28.0	20.0	10.0	24	27
19	G ¾	41	31.5	21.5	16.0	30	36
25	G 1	46	34.5	22.5	22.0	36	41
* 32	G 1¼	53	41.0	27.0	28.0	45	50
* 38	G 1½	58	43.0	27.0	34.0	50	60
* 50	G 2	64	50.0	30.0	45.0	63	70

接続口金具 : SR-02・SR-04

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。