

Compact Heavy Duty Castors

RoHS compliant products.

POINT

- **Toughened by surface hardening** of swivel bracket.
 - **Rotates smoothly** after a long-term fixation under a heavy load.
- Wheel with grease-packed precision ball bearings.
 - **Smooth and silent rolling** without subsequent lubrication.
- Smooth swiveling thanks to **double bearing** in the swivel head.

USE EXAMPLE

- For fixed precision machines to be occasionally relocated in a workplace, or moved as production line is rearranged.
- For heavy duty slow-moving carriers.
- Level adjuster
 - Separate unit causes no damage to the top plate of castor. Bolt size: M16

©We'll accept your custom-order. Please feel free to contact us.
 (Use "Specification Form for Custom-designed castor" at the end of this catalog.)
 ©Please feel free to ask about the product weight for each item.



Swivel with stopper
HJB-75U-YN



Swivel with threaded stem fitting (M20)
HJ-SJ-50U-YN

HJ Swivel castors



HJ-35 (available with MC and U)

HJ-50

HJ-65

HJ-75

• Color/Finish; Zinc plated with CrIII/White coating/Black coating/Chromium plated (HJ-35: available with Zinc plated with CrIII)

HJB Swivel with stopper



HJB-50

HJB-65

HJB-75

AD Level adjuster



NB Cannot be combined with HJB series. (Swivel with stopper)

AD-50

AD-65

AD-75

• Color/Finish; Zinc plated with CrIII (Black)

HJ-SJ Threaded stem fitting



HJ-SJ-50

HJ-SJ-65

HJ-SJ-75

• Color/Finish; Zinc plated with CrIII/Black coating

HJB-SJ Threaded stem fitting with stopper



HJB-SJ-50

HJB-SJ-65

HJB-SJ-75

HK Fixed castors



HK-50

HK-65

HK-75

• Color/Finish; Zinc plated with CrIII/White coating/Black coating/Chromium plated

WHEELS

JBB ...Radial ball bearing

See P.62 to P.71 for detailed description.



YN (Nylon6 + Special recycled nylon)
JBB



MC (Monomer cast nylon/Blue)
JBB



MCMO (Monomer cast nylon/Black)
JBB



U (UR/Green)
JBB