


リングシールタイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

SSO-07 (同径)




接続口金具 : SR-01

*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	dφmm	Lmm	HEXmm
6	Rc 1/4	G 1/4	11	17	5.5	28	19
9	Rc 3/8	G 3/8	11	19	8.0	30	22
12	Rc 1/2	G 1/2	15	22	11.0	37	27
19	Rc 3/4	G 3/4	16	25	16.0	41	36
25	Rc 1	G 1	18	27	22.0	45	41
* 32	Rc1 1/4	G1 1/4	20	30	28.0	50	50
* 38	Rc1 1/2	G1 1/2	22	30	34.0	52	60
* 50	Rc 2	G 2	25	36	45.0	61	70

SSO-07 (異径)




接続口金具 : SR-01

SUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	dφmm	Lmm	HEXmm
6×9	Rc1/4	G3/8	11	17	8.0	28	22
9×12	Rc3/8	G1/2	15	19	11.0	34	27
12×19	Rc1/2	G3/4	16	22	16.0	38	36
19×25	Rc3/4	G 1	18	25	22.0	43	41
9×6	Rc3/8	G1/4	11	19	5.5	30	22
12×9	Rc1/2	G3/8	11	22	8.0	33	27
19×12	Rc3/4	G1/2	15	25	11.0	40	36
25×19	Rc 1	G3/4	16	27	16.0	43	41

SSO-09 (同径)




接続口金具 : SR-05

*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
6	G 1/4	11	8	13	5.5	32	19
9	G 3/8	11	8	15	8.0	34	22
12	G 1/2	15	10	18	11.0	43	27
19	G 3/4	16	12	20	16.0	48	36
25	G 1	18	12	22	22.0	52	41
* 32	G1 1/4	20	14	24	28.0	58	50
* 38	G1 1/2	22	14	24	34.0	60	60
* 50	G 2	25	17	28	45.0	70	70

SSO-09 (異径)



接続口金具 : SR-05

SUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ φmm	d ₂ φmm	Lmm	HEXmm
6×9	G 1/4	G 3/8	11	8	13	5.5	7.0	32	22
9×12	G 3/8	G 1/2	15	10	15	7.0	10.0	40	27
12×19	G 1/2	G 3/4	16	10	18	10.0	16.0	44	36
19×25	G 3/4	G 1	18	12	20	16.0	22.0	50	41
9×6	G 3/8	G 1/4	11	8	15	7.0	5.5	34	19
12×9	G 1/2	G 3/8	11	10	18	10.0	7.0	39	22
19×12	G 3/4	G 1/2	15	12	20	16.0	10.0	47	27
25×19	G 1	G 3/4	16	12	22	22.0	16.0	50	36

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。