


リングシールタイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

SSO-13 (同径)




接続口金具 : SR-04

*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Cmm	d ₁ mm	Lmm	HEXmm
6	G ¼	11	8	16.0	5.5	35.0	19
9	G ⅜	11	8	17.5	8.0	36.5	22
12	G ½	15	10	20.0	11.0	45.0	27
19	G ¾	16	12	21.5	16.0	49.5	36
25	G 1	18	12	22.5	22.0	52.5	41
* 32	G1¼	20	14	27.0	28.0	61.0	50
* 38	G1½	22	14	27.0	34.0	63.0	60
* 50	G 2	25	17	30.0	45.0	72.0	70

SSO-13 (異径)





接続口金具 : SR-04

SUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ mm	d ₂ mm	Lmm	Hmm
6×9	G ¼	G ⅜	11	8	16.0	5.5	7.0	35.0	22
9×12	G ⅜	G ½	15	10	17.5	7.0	10.0	42.5	27
12×19	G ½	G ¾	16	10	20.0	10.0	16.0	46.0	36
19×25	G ¾	G 1	18	12	21.5	16.0	22.0	51.5	41
9×6	G ⅜	G ¼	11	8	17.5	7.0	5.5	36.5	19
12×9	G ½	G ⅜	11	10	20.0	10.0	7.0	41.0	22
19×12	G ¾	G ½	15	12	21.5	16.0	10.0	48.5	27
25×19	G 1	G ¾	16	12	22.5	22.0	16.0	50.5	36


SSO-RG



*印及びSUSは受注生産

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	d ₁ mm	Lmm	HEXmm
6	R ¼	G ¼	11	8	13	5.5	32	19
9	R ⅜	G ⅜	11	8	15	8.0	34	22
12	R ½	G ½	15	10	18	11.0	43	27
19	R ¾	G ¾	16	12	20	16.0	48	36
25	R 1	G 1	18	12	22	22.0	52	41
* 32	R1¼	G1¼	20	14	25	28.0	59	50
* 38	R1½	G1½	22	14	25	34.0	61	60
* 50	R 2	G 2	25	17	30	45.0	72	70

SSO-ORFS-UG



受注生産

呼び径	ねじT ₁ UNF	ねじT ₂ G	Lmm	Amm	Bmm	Cmm	φd ₁ mm	φd ₂ mm	HEX	リング-1 AS568	リング-2 1BP
9/16×6	9/16	¼	28.8	11	8	9.8	4.4	5.5	19.0	011	11
1 1/16×9	1 1/16	⅜	20.2	11	8	11.2	6.7	8.0	22.0	012	14
1 3/16×12	1 3/16	½	37.8	15	10	12.8	9.6	11.0	27.0	014	18
1×19	1	¾	43.5	16	12	15.5	12.3	16.0	36.0	016	24
1 9/16×19	1 9/16	¾	45.0	16	12	17.0	15.5	16.0	36.0	018	24
2 3/16×25	1 7/16	1	47.5	18	12	17.5	20.6	22.0	41.0	021	29

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。