


ストレートタイプアダプター

- Material : Plated steel.
- 材質 : SS(三価クロメートメッキ)

SR-14M (ミリねじ)




接続口金具 : SR-04(Mねじ)

SUSは受注生産

| 呼び径 | ねじT | Amm | Bmm | dφmm | Lmm | HEXmm |
|-----|----------|------|-----|------|-----|-------|
| 14 | M14-P1.5 | 16.5 | 8 | 5.5 | 41 | 19 |
| 18 | M18-P1.5 | 18.0 | 8 | 7.0 | 44 | 22 |
| 22 | M22-P1.5 | 21.0 | 10 | 10.0 | 52 | 27 |
| 24 | M24-P1.5 | 23.0 | 10 | 12.5 | 56 | 32 |
| 30 | M30-P1.5 | 28.0 | 10 | 16.0 | 66 | 36 |
| 33 | M33-P1.5 | 30.0 | 12 | 20.0 | 72 | 41 |

SR-14U (ユニファイねじ)




接続口金具 : SR-04(UNFねじ)

*印及びSUSは受注生産


| 呼び径 | ねじT UNF-UN | Amm | Bmm | dφmm | Lmm | HEXmm |
|---------|---------------|------|-----|------|------|-------|
| 3/16 | 3/16-20 | 14.0 | 7 | 4.4 | 35.0 | 17 |
| 1/2 | 1/2-20 | 14.0 | 8 | 5.5 | 36.0 | 19 |
| 9/16 | 9/16-18 | 14.1 | 8 | 7.0 | 36.2 | 19 |
| 3/4 | 3/4-16 | 16.7 | 9 | 10.0 | 42.4 | 24 |
| 7/8 | 7/8-14 | 19.3 | 10 | 10.0 | 48.6 | 27 |
| 1 1/16 | 1 1/16-12 | 21.9 | 12 | 16.0 | 55.8 | 36 |
| 1 5/16 | 1 5/16-12 | 23.1 | 12 | 22.0 | 58.2 | 41 |
| * 1 5/8 | 1 5/8-12 | 24.3 | 14 | 28.0 | 62.6 | 50 |
| * 1 7/8 | 1 7/8-12 | 27.5 | 14 | 34.0 | 69.0 | 60 |
| * 2 1/2 | 2 1/2-12 | 33.9 | 17 | 45.0 | 84.8 | 70 |

SR-14 (WID)



| 呼び径 | ねじT ₁ | ねじT ₂ | Amm | Bmm | Cmm | d ₁ φmm | d ₂ φmm | Lmm | HEXmm |
|---------|------------------|------------------|-----|-----|-----|--------------------|--------------------|-----|-------|
| W20 | W20-16 | W20-16 | 27 | 8 | 27 | 7 | 7 | 62 | 22 |
| W32 | W32-12 | W32-12 | 34 | 12 | 34 | 12 | 12 | 80 | 36 |
| W20×W32 | W20-16 | W32-12 | 34 | 12 | 27 | 7 | 12 | 73 | 36 |

SR-16 (同径)



SUSは受注生産

| 呼び径 | ねじT ₁ | ねじT ₂ | Amm | Bmm | dφmm | Lmm | HEXmm |
|-----|------------------|------------------|-----|-----|------|-----|-------|
| 6 | G 1/4 | R 1/4 | 13 | 8 | 5.5 | 38 | 19 |
| 9 | G 3/8 | R 3/8 | 15 | 8 | 7.0 | 42 | 22 |
| 12 | G 1/2 | R 1/2 | 18 | 10 | 10.0 | 50 | 27 |
| 19 | G 3/4 | R 3/4 | 20 | 12 | 16.0 | 56 | 36 |
| 25 | G 1 | R 1 | 22 | 12 | 22.0 | 60 | 41 |
| 32 | G 1 1/4 | R 1 1/4 | 25 | 14 | 28.0 | 69 | 50 |
| 38 | G 1 1/2 | R 1 1/2 | 25 | 14 | 34.0 | 72 | 60 |
| 50 | G 2 | R 2 | 30 | 17 | 45.0 | 83 | 70 |

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。