


プラグタイプアダプター


- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

ORPPU




呼び径	ねじT (UNF・UN)	Lmm	Amm	Bmm	HEXmm
7/16	7/16-20	17.0	7.9	9.1	14
1/2	1/2-20	17.0	7.9	9.1	16
9/16	9/16-18	18.5	8.6	9.9	17
3/4	3/4-16	20.3	9.2	11.1	22
7/8	7/8-14	23.6	10.9	12.7	27
1 1/16	1 1/16-12	27.7	12.6	15.1	32
1 3/16	1 3/16-12	28.4	13.3	15.1	38
1 5/8	1 5/8-12	30.5	15.4	15.1	46

ORFSP-1



呼び径	ねじT (UNS・UN UNF)	Lmm	Amm	Bmm	HEXmm		Oリング
					1	2	
9/16	9/16-18	16.7	6.9	9.8	17.0	15.9	AS568-011
1 1/16	1 1/16-16	19.2	8.0	11.2	19.0	19.1	AS568-012
1 3/16	1 3/16-16	21.8	9.0	12.8	22.0	22.2	AS568-014
1	1-14	25.9	10.4	15.5	27.0	—	AS568-016
1 9/16	1 9/16-12	27.4	10.4	17.0	32.0	31.8	AS568-018
2 3/16	1 7/8-12	27.9	10.4	17.5	38.0	38.1	AS568-021
2 7/16	1 11/16-12	27.9	10.4	17.5	46.0	44.5	AS568-025
2	2-12	27.9	10.4	17.5	54.0	—	AS568-029

ORFSP-2



呼び径	ねじT (UNS・UN・UNF)	Lmm	Amm	HEXmm	
				1	2
9/16	9/16-18	15.5	6.9	17.0	17.5
1 1/16	1 1/16-16	17.7	8.0	19.0	20.6
1 3/16	1 3/16-16	21.0	10.0	22.0	23.8
1	1-14	22.4	10.4	27.0	28.6
1 9/16	1 9/16-12	23.9	10.4	32.0	34.9
2 3/16	1 7/8-12	25.4	10.4	38.0	41.3
2 7/16	1 11/16-12	25.4	10.4	46.0	47.6
2	2-12	25.4	10.4	54.0	57.2

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。