


リングシールタイプアダプター


- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

SWO-5 (同径)




呼び径	ねじT	Amm	Bmm	Cmm	Dmm	Emm	Fmm	dφmm	HEXmm
6	G $\frac{1}{4}$	22.0	16.0	29	21	7.5	14	5.5	19
9	G $\frac{3}{8}$	24.5	17.5	33	24	8.8	19	8.0	22
12	G $\frac{1}{2}$	28.0	20.0	39	27	10.0	22	11.0	27
19	G $\frac{3}{4}$	31.5	21.5	44	30	11.0	30	16.0	32
25	G 1	34.0	22.5	47	33	12.0	36	22.0	41

SWO-5 (異径)




呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	Dmm	Emm	Fmm	d ₁ φmm	d ₂ φmm	Hmm
6×9	G $\frac{1}{4}$	G $\frac{3}{8}$	24.5	16.0	33	24	8.8	19	5.5	8.0	22
9×12	G $\frac{3}{8}$	G $\frac{1}{2}$	28.0	17.5	39	27	10.0	22	8.0	11.0	27
12×19	G $\frac{1}{2}$	G $\frac{3}{4}$	31.5	20.0	44	30	11.0	30	11.0	16.0	32
19×25	G $\frac{3}{4}$	G 1	34.0	21.5	47	33	12.0	36	16.0	22.0	41
9×6	G $\frac{3}{8}$	G $\frac{1}{4}$	24.5	17.5	33	21	7.5	19	8.0	5.5	19
12×9	G $\frac{1}{2}$	G $\frac{3}{8}$	28.0	20.0	39	24	8.8	22	11.0	8.0	22
19×12	G $\frac{3}{4}$	G $\frac{1}{2}$	31.5	21.5	44	27	10.0	30	16.0	11.0	27
25×19	G 1	G $\frac{3}{4}$	34.0	22.5	47	30	11.0	36	22.0	16.0	32

SWO-5UNF (ユニファイ)



呼び径	ねじT UNF・UN	Amm	Bmm	Cmm	Dmm	Emm	Fmm	dφmm	HEXmm
$\frac{7}{16}$	$\frac{7}{16}$ -20	21	14.0	29	19	7	14	4.5	14
$\frac{9}{16}$	$\frac{9}{16}$ -18	21	14.1	29	20	8	14	7.0	19
$\frac{3}{4}$	$\frac{3}{4}$ -16	25	16.7	33	23	9	19	10.0	24
$\frac{7}{8}$	$\frac{7}{8}$ -14	28	19.3	39	27	10	22	12.0	27
1 $\frac{1}{16}$	1 $\frac{1}{16}$ -12	32	21.9	44	30	12	30	16.0	32
1 $\frac{5}{16}$	1 $\frac{5}{16}$ -12	34	23.1	47	30	12	36	22.0	38

SWO-5GU (G×UNF)



呼び径	ねじT ₁	ねじT ₂ UNF・UN	Amm	Bmm	Cmm	Dmm	Emm	Fmm	d ₁ φmm	d ₂ φmm	Hmm
6× $\frac{7}{16}$	G $\frac{1}{4}$	$\frac{7}{16}$ -20	22.0	16.0	29	19	7	14	5.5	4.5	14
6× $\frac{9}{16}$	G $\frac{1}{4}$	$\frac{9}{16}$ -18	22.0	16.0	29	20	8	14	5.5	7.0	19
9× $\frac{3}{4}$	G $\frac{3}{8}$	$\frac{3}{4}$ -16	24.5	17.5	33	23	9	19	7.0	10.0	24
12× $\frac{7}{8}$	G $\frac{1}{2}$	$\frac{7}{8}$ -14	28.0	20.0	39	27	10	22	10.0	12.0	27
19×1 $\frac{1}{16}$	G $\frac{3}{4}$	1 $\frac{1}{16}$ -12	31.5	21.5	44	30	12	30	16.0	16.0	32
25×1 $\frac{5}{16}$	G 1	1 $\frac{5}{16}$ -12	34.0	22.5	47	30	12	36	22.0	22.0	38

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。