


Tタイプアダプター


- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

T-R-R-R





呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	ねじT <sub>3</sub>	Lmm	Amm	Bmm	Cmm	Dmm	Emm	dφmm
6	R $\frac{1}{4}$	R $\frac{1}{4}$	R $\frac{1}{4}$	46	13	20	13	23	13	5.5
9	R $\frac{3}{8}$	R $\frac{3}{8}$	R $\frac{3}{8}$	56	15	26	15	28	15	7.0
12	R $\frac{1}{2}$	R $\frac{1}{2}$	R $\frac{1}{2}$	64	18	28	18	32	18	10.0
19	R $\frac{3}{4}$	R $\frac{3}{4}$	R $\frac{3}{4}$	74	20	34	20	37	20	16.0
25	R 1	R 1	R 1	86	22	42	22	43	22	21.5

T-R-R-Rc




呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	ねじT <sub>3</sub>	Lmm	Amm	Bmm	Cmm	Dmm	dφmm
6	R $\frac{1}{4}$	R $\frac{1}{4}$	Rc $\frac{1}{4}$	50	13	24	13	23	5.5
9	R $\frac{3}{8}$	R $\frac{3}{8}$	Rc $\frac{3}{8}$	58	15	28	15	28	7.0
12	R $\frac{1}{2}$	R $\frac{1}{2}$	Rc $\frac{1}{2}$	70	18	34	18	32	10.0
19	R $\frac{3}{4}$	R $\frac{3}{4}$	Rc $\frac{3}{4}$	82	20	42	20	37	16.0

T-R-Rc-R



呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	ねじT <sub>3</sub>	Lmm	Amm	Bmm	Cmm	Dmm	dφmm
6	R $\frac{1}{4}$	Rc $\frac{1}{4}$	R $\frac{1}{4}$	48	35	13	13	25	5.5
9	R $\frac{3}{8}$	Rc $\frac{3}{8}$	R $\frac{3}{8}$	57	42	15	15	29	7.0
12	R $\frac{1}{2}$	Rc $\frac{1}{2}$	R $\frac{1}{2}$	67	49	18	18	35	10.0
19	R $\frac{3}{4}$	Rc $\frac{3}{4}$	R $\frac{3}{4}$	81	61	20	20	41	16.0

T-Rc-Rc-R



呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	ねじT <sub>3</sub>	Lmm	Amm	Bmm	Cmm	dφmm
6	Rc $\frac{1}{4}$	Rc $\frac{1}{4}$	R $\frac{1}{4}$	46	23	13	25	5.5
9	Rc $\frac{3}{8}$	Rc $\frac{3}{8}$	R $\frac{3}{8}$	56	28	15	29	7.0
12	Rc $\frac{1}{2}$	Rc $\frac{1}{2}$	R $\frac{1}{2}$	64	32	18	35	10.0
19	Rc $\frac{3}{4}$	Rc $\frac{3}{4}$	R $\frac{3}{4}$	80	40	20	41	16.0

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。