

## Stowed High Magnification Model



### Features

- Small, portable, fold-away style with high magnification
- Can increase its magnification by using multiple lenses  
75531...7x with two lenses, 10.5x with three lenses  
75766...7x with 3x + 4x, 8x with 3x + 5x, 9x with 4x + 5x, 12x with three lenses

### Use

- For high-magnification work such as jewelry inspection, or observation, drafting, etc.

### Specifications

Item Code	75523	75531	75765	75766
Lens Size (mm)	φ7	φ13	φ23	φ19
Magnification	20x	10x	3.5x	10x
Material	Body: Brass Lens: Glass	Body: ABS resin Lens: Glass	Body: Iron, zinc Lens: Glass	Body: Iron, aluminum Lens: Glass

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Packaging
75523	C Double Lens 10x/20x	58×23×16	30	4 960910 755239	5	SP
75531	D Triplet Lens 3.5x	59×28×15	16	4 960910 755314	5	SP
75765	I 10x with Chain	44×27×16	46	4 960910 757653	5	SP
75766	J 3x/4x/5x with Chain	44×27×16	47	4 960910 757660	5	SP

## Pocket Microscope



### Features

- Pocket-sized microscope with LED light  
\*Image appears upside down.
- Easily change between 60- and 100-power by adjusting the dial



### Use

- For observation outdoors or inspection of printing, etc.

### Specifications

Magnification	60 - 100x (tolerance 20%)
Light	White LED
Luminous Intensity	12,900 mcd
Material	Body: ABS resin Lens: Acrylic resin
Power Source	3x Alkaline batteries LR1130 (included) (Batteries included are for trial use only and may not last as long)

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Packaging
75753	H 60x - 100x with LED Light	83×33×20	31	4 960910 757530	5	SP

## Stand Magnifier



### Features

- Stand model frees up both hands

### Use

- For measuring small objects with 25 mm graduation (75763)
- For working on a desk with the adjustable angle lens (75539)

### Specifications

Item Code	75763	75539
Lens Size (mm)	φ25	φ65
Magnification	6x	3x
Material	Body: Aluminum Lens: Glass	Body: Brass Base: Cast metal Lens: Glass

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Packaging
75763	G 25 mm 6x	51×38×50	43	4 960910 757639	5	SP
75539	P-1 65 mm 3x	166×54×60	384	4 960910 755390	2	SP