


ステンレス

竹の子ニップル(SUS)

● Material : Stainless steel
● 材質 : SUS304 ● 用途 : 空気、油、蒸気etc. ● 耐圧力 : 低圧~中圧


7001



接続アダプター : SR-07・SR-08・SR-17・SR-18


呼び径	ねじT	Amm	Bmm	Cmm	Emm	D ₁ φmm	D ₂ φmm	D ₃ φmm	Lmm	HEXmm	山数
6	R ¼	13	7	24	5.0	4	6.0	7.5	44	14	3
9	R ⅜	15	7	28	6.0	6	9.2	10.5	50	19	3
12	R ½	18	8	36	8.0	9	12.5	14.0	62	22	3
19	R ¾	20	10	45	10.0	15	19.0	20.5	75	27	3
25	R 1	22	12	58	13.0	21	25.0	27.0	92	35	3
32	R1¼	25	12	65	14.5	27	32.0	34.0	102	46	3
38	R1½	26	14	76	14.0	31	38.0	40.3	116	50	4
50	R 2	30	15	79	14.5	44	49.5	52.0	124	63	4
65	R2½	33	16	91	14.0	56	62.5	65.0	140	80	5
75	R 3	38	16	106	16.0	69	74.5	77.5	160	90	5

7005



呼び径	ねじT	Amm	Bmm	Cmm	D ₁ φmm	D ₂ φmm	D ₃ φmm	Lmm	HEXmm	山数
6	G ¼	32	17	5.0	4	6.0	7.5	41	19	3
9	G ⅜	36	18	6.0	7	9.2	10.5	46	22	3
12	G ½	45	21	8.0	10	12.5	14.0	57	27	3
19	G ¾	56	24	10.0	15	19.0	20.5	69	32	3
25	G 1	71	28	13.0	21	25.0	27.0	86	38	3
32	G1¼	80	31	14.5	28	32.0	34.0	96	50	3
38	G1½	91	31	14.0	33	38.0	40.3	107	60	4
50	G 2	94	33	14.5	44	49.5	52.0	112	70	4
65	G2½	108	40	14.0	56	62.5	65.0	131	90	5
75	G 3	124	42	16.0	69	74.5	77.5	148	100	5


7006



接続アダプター : SR-13・SR-14・SR-17・SR-33・SR-35

呼び径	ねじT	Amm	Bmm	Cmm	D ₁ φmm	D ₂ φmm	D ₃ φmm	Lmm	HEXmm	山数
6	G ¼	32	17	5.0	4	6.0	7.5	41	19	3
9	G ⅜	36	18	6.0	7	9.2	10.5	46	22	3
12	G ½	45	21	8.0	10	12.5	14.0	57	27	3
19	G ¾	56	24	10.0	15	19.0	20.5	69	32	3
25	G 1	71	28	13.0	21	25.0	27.0	86	38	3
32	G1¼	80	31	14.5	28	32.0	34.0	96	50	3
38	G1½	91	31	14.0	33	38.0	40.3	107	60	4
50	G 2	94	33	14.5	44	49.5	52.0	112	70	4
65	G2½	108	40	14.0	56	62.5	65.0	131	90	5
75	G 3	124	42	16.0	69	74.5	77.5	148	100	5

7007



接続アダプター : SR-07・SR-09・SR-11・SR-34・SR-36

呼び径	ねじT	Amm	Bmm	Cmm	D ₁ φmm	D ₂ φmm	D ₃ φmm	Lmm	HEXmm	山数
6	G ¼	35	17	5.0	4	6.0	7.5	41	19	3
9	G ⅜	40	18	6.0	7	9.2	10.5	46	22	3
12	G ½	49	21	8.0	10	12.5	14.0	57	27	3
19	G ¾	61	24	10.0	15	19.0	20.5	69	32	3
25	G 1	75	28	13.0	21	25.0	27.0	86	38	3
32	G1¼	85	31	14.5	28	32.0	34.0	96	50	3
38	G1½	96	31	14.0	33	38.0	40.3	107	60	4
50	G 2	99	33	14.5	44	49.5	52.0	112	70	4
65	G2½	117	40	14.0	56	62.5	65.0	131	90	5
75	G 3	133	42	16.0	69	74.5	77.5	148	100	5

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。