


Super Tom Spatter Hose

Compared to conventional air hoses, this hose has greater resistance against sparks due to the inclusion of spark resistance substances, which is appropriate for using at welding sites and automobile service garages, etc.



Specialized elastomer product

Specifications: Working temperature limit: Between -40°C and +60°C

Nominal designation	Inner diameter (mm)	Outer diameter (mm)	Regular size (m)	Maximum working pressure MPa at 20°C	Burst pressure MPa at 20°C	Minimum bending radius (mm)	Weight (kg/m)	Regular size weight (kg)
STH-6510	6.5	10.0	100	1.5	7.2	30	0.057	5.7
STH-8512	8.5	12.5	100	1.5	7.6	40	0.083	8.3

Performance evaluation

Descriptions	Evaluation	Descriptions	Evaluation
Lightness	★ ★ ★ ★ ★	Smoothness	★ ★ ★ ★ ★
Softness	★ ★ ★ ★ ★	Spattering resistance	★ ★ ★ ★ ★

* All the evaluations were made in-house
* Use our specified brackets



With the specialized material containing spark resistance substances, this hose is appropriate for using at welding sites.

Usege For air-paint, air-spray, and in-factory air tools

Features Compared to conventional urethane hoses, this hose has greater resistance against sparks due to the inclusion of spark resistance substances, which is appropriate for using at welding sites and automobile service garages, etc.

Fluids Air

Takumi Air Reel



Air reel product

Usege

For air-paint, air-spray, and in-factory air tools.

Features

Reels with rotation function, you can choose the direction. Super flexible hose 'Takumi' Air Hose attached.

Fluids

Air

Quattro Reel



Air reel product

Usege

For air-paint, air-spray, and in-factory air tools.

Features

Reels with rotation function, you can choose the direction. High pressure and super flexible hose Quattro Hose attached.

Fluids

Air

Specifications: Working temperature limit: Between -5°C and +60°C

Nominal designation	Hose size	Regular size (m)	Maximum working pressure MPa at 20°C	Regular size weight (kg)
Takumi Air Reel	6.5×10	30	1.5	8.0

Nominal designation	Hose size	Regular size (m)	Maximum working pressure MPa at 20°C	Regular size weight (kg)
Quattro Reel	6.0×10	30	4.0	8.3

Sun Tech Air Reel



Air reel product

Usege

For air-paint, air-spray, and in-factory air tools.


Features

Reels with rotation function, you can choose the direction. Sun Tech Air Hose attached. You can order the reel stand without a hose.

Fluids

Air

Connect Tube (CH)



Polyurethane product

Usege

A tube for various pneumatic machines

Features

Superior in oil resistance, this tube is appropriate for in-factory air piping.

Fluids

Air

Specifications: Standard type:

Working temperature limit: Between -40°C and +80°C

(Standard length: 100m)

Nominal designation	Hose size	Regular size (m)	Maximum working pressure MPa at 20°C	Regular size weight (kg)
Sun Tech Air Reel	7.0×10	30	1.5	7.8

Nominal designation	Outer diameter (mm)	Inner diameter (mm)	Maximum working pressure MPa at 20°C	Burst pressure MPa at 20°C	Minimum bending radius (mm)	Regular size (m)	Weight (kg/m)
CH-4 BK	4.0	2.5	0.7	3.0	10	100	0.009
CH-6 BK	6.0	4.0	0.7	3.5	15	100	0.019
CH-8 BK	8.0	5.0	0.7	3.5	24	100	0.037
CH-10 BK	10.0	6.5	0.7	3.0	30	100	0.054
CH-12 BK	12.0	8.0	0.7	3.0	36	100	0.075