


# Ductile Caster for Heavy Loads

## Caster for Heavy Loads



## TB Rubber (with bearing)

unit:mm

Wheel diameter	Type	Load capacity	Wheel width	Hub length	Axle hole diameter	Boss diameter	Bearing No
100	100×50TB	140kg	50	65	17	47	CB1740
	100×65TB	180kg	65	76			
125	125×50TB	180kg	50	65	25	64	CB2552R
	125×65TB	220kg	65	76			
150	150×50TB	210kg	50	65	25	64	CB2552R
	150×65TB	250kg	65	76			
	150×75TB	310kg	76	90			
180	180×50TB	250kg	50	65	25	64	CB2552R
	180×65TB	280kg	65	76			
	180×75TB	350kg	76	90			
200	200×50TB	280kg	50	65	25	64	#6205
	200×65TB	320kg	65	76			
	200×75TB	380kg	76	90			
	200×90TB	510kg	90	100			
250	250×65TB	400kg	65	76	30	76	#6206
	250×75TB	470kg	76	90			
	250×90TB	580kg	90	100			
300	300×75TB	540kg	76	90	30	77	#6206
	300×90TB	620kg	90	100		81	
	300×100TB	900kg	102	114			
350	350×50TB	480kg	50	65	30	76	#6206
	350×65TB	550kg	65	76		78	
	350×75TB	570kg	76	90			
	350×90TB	610kg	90	100		35	
400	400×65TB	610kg	65	76	35	88	#6207
	400×75TB	660kg	76	90		90	
	400×90TB	690kg	90	100	40	98	#6208
	400×100TB	810kg	100	115			
	400×125TB	1100kg	125	140			
450	450×75TB	700kg	76	90	40	100	#6208
	450×90TB	720kg	90	100		102	
	450×100TB	1100kg	100	115			
500	500×75TB	850kg	76	90	40	102	#6208
	500×100TB	1150kg	100	115			
	500×125TB	1350kg	125	140	50	112	#6210