


DIMENSIONS OF APPARATUS TO WHICH A SGK FLANGE IS ATTACHED (FOR REFERENCE)

●AC/RX/KC series




Flange	d		R	O	P	m	t		K	
	RX	AC					RX	AC	RX	AC
10A	-	12	25	62	45	8	-	11	-	M8
15A	12.5	12	25	62	45	8	10	11	M8	M8
20A	18	18	30	74	54	8	12	13	M10	M10
25A	22	24	35	80	60	9	12	14	M10	M10
32A	30	34	50	96	75	9	14	16	M10	M10
40A	35	34	50	96	75	9	14	16	M10	M10
50A	48	46	65	120	95	10	14	19	M12	M12
65A	58	60	80	136	110	12	16	20	M12	M12
80A	68	72	90	154	125	15	20	20	M12	6-M12

Dimensions of the apparatus	d'		R'	P	m'	Z
	RX	AC				
10A	-	12	25	45	7	12
15A	12.5	12	25	45	7	12
20A	18	18	30	54	7	16
25A	22	24	35	60	8	16
32A	30	34	50	75	8	16
40A	35	34	50	75	8	16
50A	48	46	65	95	9	19
65A	58	60	80	110	11	19
80A	68	72	90	125	14	19

Dimension of $\phi R'$: $\begin{matrix} +0.05 \\ 0 \end{matrix}$

●NC series



Flange	d	R	O	P	m	t	K
15A	14	25	74	54	9	12	M10
20A	17	26	74	54	8	12	M10
25A	22	34	80	60	8	12	M10
32A	30	42	96	75	10	14	M10
40A	35	48	96	75	10	14	M10
50A	48	60	120	95	12	14	M12
65A	60	75	136	110	16	16	M12
80A	72	90	154	125	22	20	6-M12

Dimensions of the apparatus	d'	R'	P	m'	Z
15A	14	25	54	8	16
20A	17	26	54	7	16
25A	22	34	60	7	16
32A	30	42	75	9	16
40A	35	48	75	9	16
50A	48	60	95	11	19
65A	60	75	110	13	19
80A	72	90	125	15	19

Dimension of $\phi R'$: $\begin{matrix} +0.05 \\ 0 \end{matrix}$