

Disk Papers

For Disc Grinders, see p. 5-209 to 226/For Adapter, see p. 5-921 The number next to the logo mark indicates items in stock for each brand.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes



Stock 38,650 Items

Disc Paper "GP Top" Tokumaru-Kun



GP100TM (alundum (for general metal))

Estimated Unit Price per Sheet
¥345



GP100TMZ (zirconia (for stainless steel, difficult-to-cut material))

Estimated Unit Price per Sheet
¥365

Features •An economical type that has almost the same performance with GP top® and achieved further cost reduction due to efficiency improvement of the production process.
Use •Bead removal of welded surfaces. •Paint and rust remover.
Specs •Grinding Angle: 15 to 30° •Max Working Peripheral Velocity: 72m/s (4300m/min)
Accessories •Including 10 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
Origin •Japan

Alundum (for general metal)

Use •Heavy grinding, metal polishing by disc grinder. •Polishing of aircraft, automobiles, hulls, bridges and tanks, etc.
•Scale removal and various burr removal of metal. •Others, polishing of iron and steel and non-ferrous metals.

Order Unit: 1 Box

| Order Code | Item No. | OP | Price (per box) | MSRP (per box) | Grain Size (#) | Outer Diameter x Blade Length x Hole Diameter (mm) | Max Working Rotation Speed (rpm) | Blade Number (sheet) | Q'ty Per Box (sheet) | SPQ (box) | Weight (g/box) |
|------------|----------|-----|-----------------|----------------|----------------|--|----------------------------------|----------------------|----------------------|-----------|----------------|
| 220-9446 | GP100TM | 40 | ¥3,443 | ¥4,250 | 40 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 693 |
| 220-9454 | GP100TM | 60 | ¥3,443 | ¥4,250 | 60 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 612 |
| 220-9462 | GP100TM | 80 | ¥3,443 | ¥4,250 | 80 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 556 |
| 220-9471 | GP100TM | 100 | ¥3,443 | ¥4,250 | 100 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 534 |
| 220-9489 | GP100TM | 120 | ¥3,443 | ¥4,250 | 120 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 532 |
| 220-9497 | GP100TM | 150 | ¥3,443 | ¥4,250 | 150 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 532 |
| 220-9501 | GP100TM | 180 | ¥3,443 | ¥4,250 | 180 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 532 |
| 220-9519 | GP100TM | 240 | ¥3,443 | ¥4,250 | 240 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 502 |
| 220-9527 | GP100TM | 320 | ¥3,443 | ¥4,250 | 320 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 500 |
| 220-9535 | GP100TM | 400 | ¥3,443 | ¥4,250 | 400 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 470 |

TRUSCO NAKAYAMA CORPORATION

Zirconia (for stainless steel/difficult-to-cut material)

Features •Zirconia abrasive grain is used, heavy grinding and long life.
Use •Black skin removal of metal.
•Grinding and polishing of various metals such as stainless steel.

Order Unit: 1 Box

| Order Code | Item No. | OP | Price (per box) | MSRP (per box) | Grain Size (#) | Outer Diameter x Blade Length x Hole Diameter (mm) | Max Working Rotation Speed (rpm) | Blade Number (sheet) | Q'ty Per Box (sheet) | SPQ (box) | Weight (g/box) |
|------------|----------|-----|-----------------|----------------|----------------|--|----------------------------------|----------------------|----------------------|-----------|----------------|
| 284-8180 | GP100TMZ | 40 | ¥3,645 | ¥4,500 | 40 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 703 |
| 284-8198 | GP100TMZ | 60 | ¥3,645 | ¥4,500 | 60 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 653 |
| 284-8201 | GP100TMZ | 80 | ¥3,645 | ¥4,500 | 80 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 603 |
| 284-8210 | GP100TMZ | 100 | ¥3,645 | ¥4,500 | 100 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 603 |
| 284-8228 | GP100TMZ | 120 | ¥3,645 | ¥4,500 | 120 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 603 |

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Disc Paper "GP Top" Tokumaru-Kun (conical type)



GPK10016 (alundum (for general metal))

Estimated Unit Price per Sheet
¥345 to ¥1,166



GPK10016Z (zirconia (for stainless steel, difficult-to-cut material))

Estimated Unit Price per Sheet
¥365 to ¥1,301



(side)

Cross-Sectional View
Grinding on the surface against the work piece can be done



Conical (conical shape)

Features •Since it is a tapered circuit board, work can be conducted in flat surface without engraving even if the work angle is high.
•Since the outer circumference and inner side of the polished surface will wear at the same time, it is excellent in durability and can be used until the end.
Use •Metal black layer removal, bead removal on welding masks.
Specs •Working Angle: 15 to 25°
Accessories •Only Φ100mm adapter for 15mm hole 10 pieces per box (sold separately 5 pieces: GPTAS-5P)
Origin •Japan

Alundum (for general metal)

Use •Rust remover, grinding and polishing of various metal.
Specs •Maximum working peripheral velocity: GPK10016: 72m/s (4300m/min) GPK18022: 80m/s (4800m/min)

Order Unit: 1 Box

| Order Code | Item No. | OP | Price (per box) | MSRP (per box) | Grain Size (#) | Outer Diameter x Blade Length x Hole Diameter (mm) | Max Working Rotation Speed (rpm) | Blade Number (sheet) | Q'ty Per Box (sheet) | SPQ (box) | Weight (g/box) |
|------------|----------|-----|-----------------|----------------|----------------|--|----------------------------------|----------------------|----------------------|-----------|----------------|
| 287-9174 | GPK10016 | 40 | ¥3,443 | ¥4,250 | 40 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 793 |
| 287-9182 | GPK10016 | 60 | ¥3,443 | ¥4,250 | 60 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 743 |
| 287-9191 | GPK10016 | 80 | ¥3,443 | ¥4,250 | 80 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 683 |
| 287-9204 | GPK10016 | 100 | ¥3,443 | ¥4,250 | 100 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 633 |
| 287-9212 | GPK10016 | 120 | ¥3,443 | ¥4,250 | 120 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 623 |
| 287-9263 | GPK18022 | 40 | ¥5,832 | ¥7,200 | 40 | 180 x 20 x 22 | 8400 | 90 | 5 | 5 | 1628 |
| 287-9271 | GPK18022 | 60 | ¥5,832 | ¥7,200 | 60 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1378 |
| 287-9280 | GPK18022 | 80 | ¥5,832 | ¥7,200 | 80 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1328 |
| 287-9298 | GPK18022 | 100 | ¥5,832 | ¥7,200 | 100 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1278 |
| 287-9301 | GPK18022 | 120 | ¥5,832 | ¥7,200 | 120 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1178 |

Zirconia (for stainless steel/difficult-to-cut material)

Use •Grinding and polishing of difficult-to-cut material such as stainless steel.
Specs •Maximum working peripheral velocity: GPK10016Z: 72m/s (4300m/min) GPK18022Z: 80m/s (4800m/min)

Order Unit: 1 Box

| Order Code | Item No. | OP | Price (per box) | MSRP (per box) | Grain Size (#) | Outer Diameter x Blade Length x Hole Diameter (mm) | Max Working Rotation Speed (rpm) | Blade Number (sheet) | Q'ty Per Box (sheet) | SPQ (box) | Weight (g/box) |
|------------|-----------|----|-----------------|----------------|----------------|--|----------------------------------|----------------------|----------------------|-----------|----------------|
| 287-9221 | GPK10016Z | 36 | ¥4,050 | ¥5,000 | 36 | 100 x 16 x 16 | 13600 | 60 | 10 | 10 | 853 |
| 287-9239 | GPK10016Z | 40 | ¥3,645 | ¥4,500 | 40 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 813 |
| 287-9247 | GPK10016Z | 60 | ¥3,645 | ¥4,500 | 60 | 100 x 16 x 16 | 13600 | 72 | 10 | 10 | 763 |
| 287-9255 | GPK10016Z | 80 | ¥3,645 | ¥4,500 | 80 | 100 x 16 x 16 | 13600 | 80 | 10 | 10 | 743 |
| 287-9310 | GPK18022Z | 36 | ¥6,505 | ¥8,030 | 36 | 180 x 20 x 22 | 8400 | 90 | 5 | 5 | 1778 |
| 287-9328 | GPK18022Z | 40 | ¥5,954 | ¥7,350 | 40 | 180 x 20 x 22 | 8400 | 90 | 5 | 5 | 1628 |
| 287-9336 | GPK18022Z | 60 | ¥5,954 | ¥7,350 | 60 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1478 |
| 287-9344 | GPK18022Z | 80 | ¥5,954 | ¥7,350 | 80 | 180 x 20 x 22 | 8400 | 120 | 5 | 5 | 1428 |

Contact us:0120-509-849 <http://www.orange-book.com/>