

Disk Papers

For Disc Grinders, see p. 5-209 to 226/For Adapter, see p. 5-921 The number next to the logo mark indicates items in stock for each brand.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

TRUSCO Stock 38,650 Items

Disc Paper "GP Top[®]"



TGP10015-CC-80

Estimated Unit Price per Sheet
¥567

- Features**
- Rich in particle size variation, it is a versatile type that covers from rough finishing to finish polishing.
 - Due to air cooling effect, almost no work distortion and burning due to heat.
- Use**
- Polishing of glass, stone materials.
- Specs**
- Working Angle: 15 to 30°
 - Maximum working peripheral velocity: TGP10015: 72m/s (4300m/min)
- Materials**
- Silicon carbide abrasive material
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
409-8081	TGP10015-CC-40	¥2,835	¥3,500	40	100 x 16.5 x 16	13600	72	5	20	325
409-8102	TGP10015-CC-60	¥2,835	¥3,500	60	100 x 16.5 x 16	13600	80	5	20	315
409-8111	TGP10015-CC-80	¥2,835	¥3,500	80	100 x 16.5 x 16	13600	90	5	20	305
409-8021	TGP10015-CC-100	¥2,835	¥3,500	100	100 x 16.5 x 16	13600	90	5	20	285
409-8030	TGP10015-CC-120	¥2,835	¥3,500	120	100 x 16.5 x 16	13600	90	5	20	280
409-8048	TGP10015-CC-150	¥2,835	¥3,500	150	100 x 16.5 x 16	13600	90	5	20	265
409-8056	TGP10015-CC-180	¥2,835	¥3,500	180	100 x 16.5 x 16	13600	90	5	20	265
409-8064	TGP10015-CC-240	¥2,835	¥3,500	240	100 x 16.5 x 16	13600	90	5	20	265
409-8072	TGP10015-CC-320	¥2,835	¥3,500	320	100 x 16.5 x 16	13600	90	5	20	265
409-8099	TGP10015-CC-400	¥2,835	¥3,500	400	100 x 16.5 x 16	13600	90	5	20	255

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Disc Paper "GP Top[®] DX"




GP100DX (alundum (for general metal))

Estimated Unit Price per Sheet
¥648

- Features**
- With performance that is almost same as with GP top[®], can be used for about 18% longer than GP top[®] due to adoption of special plate (can grind up to 75mm in outer diameter).
 - Professional abrasive which is planted one by one by hand
- Use**
- Metal polishing, removal of welding beads, polishing of automobiles, hulls, tanks, various burring and other polishing of stainless steel, steel and non-ferrous metals.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Accessories**
- Including 5 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
- Origin**
- Japan

Since the area of the plate is smaller than GP Top[®], the abrasive can be used more widely for a long time.



Two Layer Structure of Circuit Board + Wear Circuit Board

GP Top[®] DX (deluxe) has a two-layer structure consisting of a base + wear base to enable work with the same touch as GP Top[®] from the beginning to the end of use while also being a long life type (economical type) that uses the paper down to an outer diameter of 75mm.

Alundum (for general metal)

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
172-9179	GP100DX	40	¥3,240	¥4,000	40	100 x 16.5 x 16	13600	80	5	20	350
172-9187	GP100DX	60	¥3,240	¥4,000	60	100 x 16.5 x 16	13600	90	5	20	320
172-9195	GP100DX	80	¥3,240	¥4,000	80	100 x 16.5 x 16	13600	90	5	20	300
172-9209	GP100DX	100	¥3,240	¥4,000	100	100 x 16.5 x 16	13600	90	5	20	290
172-9217	GP100DX	120	¥3,240	¥4,000	120	100 x 16.5 x 16	13600	90	5	20	260
172-9225	GP100DX	150	¥3,240	¥4,000	150	100 x 16.5 x 16	13600	90	5	20	265
172-9233	GP100DX	180	¥3,240	¥4,000	180	100 x 16.5 x 16	13600	90	5	20	270
172-9241	GP100DX	240	¥3,240	¥4,000	240	100 x 16.5 x 16	13600	90	5	20	270
172-9250	GP100DX	320	¥3,240	¥4,000	320	100 x 16.5 x 16	13600	90	5	20	260
172-9268	GP100DX	400	¥3,240	¥4,000	400	100 x 16.5 x 16	13600	90	5	20	250

Zirconia (for heavy polishing)

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
172-9276	GP100DXZ	40	¥3,240	¥4,000	40	100 x 16.5 x 16	13600	72	5	20	360
172-9284	GP100DXZ	60	¥3,240	¥4,000	60	100 x 16.5 x 16	13600	80	5	20	330
172-9292	GP100DXZ	80	¥3,240	¥4,000	80	100 x 16.5 x 16	13600	90	5	20	315

Contact us:0120-509-849 <http://www.orange-book.com/>