


Impact Drivers / Drivers Ratchet Wrenches




MID-8P 1/4"Hex

- 2 hammer(Pin-less)clutch
- 2 steps throttle for precise control
- 360 free rotating handle exhaust
- Well balanced Ergonomic design
- One handed easy reverse switch
- Ideal for wood work and assembly work
- 3/8 SQ.drive model available(MID-8P(R) 3/8SQ)



MI-12D 1/4"Hex





- Twin hammer clutch
- Tease throttle for precise control
- Handle Exhaust directs air away from an operator
- Well balanced Ergonomic design
- 4 Positions regulator
- Elastomer handle grip
- 3/8 SQ.drive model available (MID-12P 3/8SQ)
- Ideal for wood work and assembly work



MID-60 1/4"Hex

- Ideal for motor vehicle and light assembly work



- Ideal for furniture,wood working, motor vehicle and other assembly operations



MV-6216 1/4"Hex

- Ideal for appliance,electronics and other light assembly industries

MV-6226 1/4"Hex

- Easy grip handle Quick run down capacity
- Ideal for usage on pumps, radiators, small engines exhaust systems etc.



MR-2207C 1/4"SQ
MR-2209C 3/8"SQ

- Compact and powerful
- Rubber covered ratchet head
- Durable ratchet head (heat treated) prevents slipping
- Ideal for confined working conditions



MR-2310B 3/8"SQ
MR-2410B 1/2"SQ

Impact Drivers Specifications: Air pressure 6kg/cm²

MODEL	Drive (in)	Bolt Size (mm)	Net Weight (kg)	Overall Length (mm)	Center Height (mm)	Free Speed (rpm)	Air Cons		Air Inlet (PT)	Hose Size (in)
							Free (m ³ /min)	Load (m ³ /min)		
MID-8P	H 1/4	8	1.0	154	22.5	10500	0.55	0.4	1/4	1/4
MI-12D	H 1/4	12	1.2	154	25.3	9500	0.50	0.4	1/4	1/4
MID-60	1/4	6	0.8	181	55	10800	0.48	0.32	1/4	3/8

Drivers and Ratchet Wrenches Specifications: Air pressure 6kg/cm²

MODEL	Drive (in)	Bolt Size (mm)	Torque Range (kg·m)	Net Weight (kg)	Overall Length (mm)	Free Speed (rpm)	Air Cons (m ³ /min)	Air Inlet (PT)	Hose Size (in)
MV-6216	H1/4	6	0.4-0.9	1.2	250	1800	0.42	1/4	1/4
MV-6226	H1/4	6	0.5-1.2	1.3	205	1800	0.6	1/4	1/4
MR-2207C	1/4	8	0.6-2.8	0.53	165	250	0.35	1/4	1/4
MR-2209C	3/8	8	0.6-2.8	0.53	165	250	0.35	1/4	1/4
MR-2310B	3/8	10	1.4-7.0	1.13	254	180	0.45	1/4	1/4
MR-2410B	1/2	10	1.4-7.0	1.13	254	180	0.45	1/4	1/4