

Papers for Double Action Sander

For Double Action Sanders, see p.5-16 to 530

The number next to the logo mark indicates items in stock for each brand.

Abrasives

TRUSCO



Stock 38,650 Items

"Magis Disc"



- Features**
- Can replace the count with a single touch.
 - Cutting quality is sharp.
 - Abrasion marks are hard to come out.
 - Low clogging and long service life.
- Use**
- Grain size #120 to #1000 is water resistance and can be used with water.
 - Automobile repair and polishing work.
 - Various grinding work in woodwork and furniture manufacturers.
 - Polishing work in building painting and interior construction.
 - Coating film polishing in various vehicles.
 - Metal baking paint polishing work.
- Specs**
- Max Working Peripheral Velocity: 26.2m/s (1572m/min)
- Origin**
- Japan



TMD50-100

Outer Diameter 50mm
Estimated Unit Price per Sheet
¥21 to ¥24

Outer Diameter 50mm

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Color	Outer Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
287-8755	TMD50-60	¥2,407	¥2,600	60	Ash	50	10000	100	1	160
287-8763	TMD50-80	¥2,083	¥2,250	80	Ash	50	10000	100	1	130
287-8771	TMD50-100	¥2,083	¥2,250	100	Ash	50	10000	100	1	120
287-8780	TMD50-120	¥2,083	¥2,250	120	Ash	50	10000	100	1	100
287-8798	TMD50-180	¥2,083	¥2,250	180	Ash	50	10000	100	1	90
287-8801	TMD50-240	¥2,083	¥2,250	240	Ash	50	10000	100	1	80
287-8810	TMD50-320	¥2,083	¥2,250	320	Ash	50	10000	100	1	70
287-8828	TMD50-400	¥2,083	¥2,250	400	Ash	50	10000	100	1	70
287-8836	TMD50-600	¥2,083	¥2,250	600	Ash	50	10000	100	1	60
287-8844	TMD50-1000	¥2,083	¥2,250	1000	Ash	50	10000	100	1	60

Outer Diameter 75mm

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Color	Outer Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
856-3579	TMD75-60	¥2,685	¥2,900	60	Ash	75	10000	50	10	180
856-3580	TMD75-80	¥2,592	¥2,800	80	Ash	75	10000	50	10	160
856-3581	TMD75-100	¥2,592	¥2,800	100	Ash	75	10000	50	10	390
856-3582	TMD75-120	¥2,592	¥2,800	120	Ash	75	10000	50	10	330
856-3583	TMD75-180	¥2,592	¥2,800	180	Ash	75	10000	50	10	300
856-3584	TMD75-240	¥2,592	¥2,800	240	Ash	75	10000	50	10	250
856-3585	TMD75-320	¥2,592	¥2,800	320	Ash	75	10000	50	10	240
856-3586	TMD75-400	¥2,592	¥2,800	400	Ash	75	10000	50	10	200

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

"Fabric Disc"



- Features**
- Since it is based on non-woven nylon fabric and alundum abrasive grain, it can perform soft polishing work and it fits well in the work piece.
 - Attaches to the pad with Velcro tape and uses.
- Use**
- Thin rust removal of metal product, glossy appearance.
 - Fuzz removal of woodwork products.
- Specs**
- Max Working Peripheral Velocity: 26.2m/s (1572m/min)
- Materials**
- Abrasive: Alundum Abrasive Grain (A)
 - Nylon non woven fabric
- Origin**
- Japan



TFD-125: 320 (brown)



TFD-125: 600 (blue green)

Estimated Unit Price per Sheet
¥208

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per bag)	MSRP (per bag)	Grain Size (#)	Color	Outer Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
258-4107	TFD-125	320	¥417	¥450	320	Brown	125	4000	2	15	20
258-4115	TFD-125	600	¥417	¥450	600	Blue Green	125	4000	2	15	20

Contact us: 0120-509-849 <http://www.orange-book.com/>

3M



Stock 4,068 Items

3M™ "Hook-it™ Trizact™ Finishing Disc"

- Features**
- The mist sanding method which gently moistens the surface of the abrasive material and the painted surface with mist blowing designs a three-dimensional structure so that polishing residue is discharged along the groove together with water.
 - Since it does not create deep scratches and realizes an extremely stable polished grain, it is suitable for the work of removing grains during polishing.
- Specs**
- Maximum working peripheral velocity: 59.8m/s (3589m/min)
 - One Touch Type
 - No hole
- Materials**
- Base material: 2mm sponge
 - Abrasive material: silicon carbide
- Origin**
- USA



2096 (gray)

Order Unit: 15 Sheets

3M JAPAN LIMITED

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Color	Outer Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
796-1057	2096	¥464*	¥430*	15	3000	Gray	127	9000	2
796-1081	30562	¥670*	¥620*	15	5000	Light Blue	127	9000	8

Contact us: 0570-011-211 <http://www.mmm.co.jp/aad/>