

Prices displayed include 8% tax.

For Saber Saw Main Bodies, see p. 5-324 to 336

Cutting Supplies

Cutting Wheels

Tip Saws

Diamond Cutters

Metal Saws

Band Saws

Machine Saws

Hand Hacksaws

Saw Blades


Air Saw Blades

Jig Saw Blades

! Please wear protective equipment to use safely.

TRUSCO Stock 38,650 Items

Bimetal Saber Saw Blade



TBS-200-14-5P

- Features**
- Difficult to chip or snap so it reduces the work of replacing it.
 - A bimetal mechanism consisting of cobalt high-speed steel on the blade edge and special spring steel on the back.
 - Suitable for a wide variety of work materials.
- Use**
- For cutting work of stainless steel pipe, stainless steel material, steel pipe material, nonferrous metal steel material, etc. For demolition site work.
- Specs**
- Compatible Model Manufacturer: Makita, HITACHI, RYOBI, BOSCH
 - Used Electric Tool: Saber Saw, Reciprocating Saw
- Materials Origin**
- Bimetal High-Speed Steel
 - Japan

Estimated Unit Price per Sheet
¥542 to ¥852

TRUSCO NAKAYAMA CORPORATION


Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)			Q'ty Per Bag (sheet)	Weight (g/bag)
								Stainless Steel Materials	Steel Material	Stainless Steel Pipe Material		
767-9181	TBS-160-14-5P	¥2,712	¥2,930	14	160	0.9	140	2.5	3.0 to 8.0	60	5	98
767-9190	TBS-160-18-5P	¥2,712	¥2,930	18	160	0.9	140	2.5	1.5 to 4.0	60	5	98
767-9203	TBS-200-14-5P	¥3,333	¥3,600	14	200	0.9	180	2.5	3.0 to 8.0	115	5	125
767-9211	TBS-200-18-5P	¥3,333	¥3,600	18	200	0.9	180	2.5	1.5 to 4.0	115	5	125
767-9220	TBS-250-14-5P	¥3,842	¥4,150	14	250	0.9	230	2.5	3.0 to 8.0	150	5	157
767-9238	TBS-250-18-5P	¥3,842	¥4,150	18	250	0.9	230	2.5	1.5 to 4.0	150	5	157
767-9246	TBS-300-14-5P	¥4,258	¥4,600	14	300	0.9	280	2.5	3.0 to 8.0	175	5	190
767-9254	TBS-300-18-5P	¥4,258	¥4,600	18	300	0.9	280	2.5	1.5 to 4.0	175	5	190

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

"Wide Bimetal Saber Saw Blade for Dismantling"



TBS-228-14-HST-5P

- Features**
- It is harder to shake by extending width and thickness than ordinary saver saws, and it is possible to extend the life of the blade.
 - Due to flexible bimetal material, it is suitable for cutting various materials with such as demolition.
 - For those where 9mm is too easy to snap but 1.3mm is too heavy.
 - A wide blade that is about 20% more than conventional products.
 - Precision polished tooth with a sharp cut, realizes a quick sharpness.
- Use**
- For cutting work of stainless steel pipe, stainless steel material, steel pipe material, nonferrous metal steel material, etc.
 - For demolition site work.
- Specs**
- Compatible Model Manufacturer: Makita, HITACHI, RYOBI, BOSCH Saber Saws and Reciprocating Saws
- Materials Origin**
- Bimetal High-Speed Steel
 - Sweden

Estimated Unit Price per Sheet
¥666 to ¥926

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)			Q'ty Per Bag (sheet)	Weight (g/bag)
								Stainless Steel Pipe Materials, Iron	Stainless Steel Pipe Materials, Iron	Stainless Steel Pipe Materials, Iron		
819-5243	TBS-150-14-HST-5P	¥3,333	¥3,600	14	150	1.1	130	10 to 20			5	140
819-5244	TBS-228-14-HST-5P	¥4,166	¥4,500	14	228	1.1	200	10 to 20			5	211
819-5245	TBS-300-14-HST-5P	¥4,629	¥5,000	14	300	1.1	280	10 to 20			5	280

Contact us: 0120-509-849 <http://www.orange-book.com/>

HITACHI Stock 1,174 Items

Saber Saw Blade



0095-9800

- Features**
- Replacement blade for HITACHI saber saws.
 - A straight type.
- Origin**
- Japan

Estimated Unit Price per Sheet
¥527 to ¥1,013

For Thin Stainless Steel

- Use**
- For cutting stainless steel and dismantling work.
- Materials**
- High-Speed Steel

Order Unit: 1 Bag

HITACHI KOKI Co.Ltd.

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)					Q'ty Per Bag (sheet)	Weight (g/bag)
								Non-Ferrous Metal Steel Material	Stainless Steel Materials	Steel Material	Steel Pipe	Stainless Steel Pipe Material		
767-8975	0095-9800	¥2,633	¥2,600	18	120	0.9	54	5 to 20	to 2.5	2.5 to 19	to 40	to 40	3	440
767-8967	0095-9799	¥3,038	¥3,000	18	195	0.9	129	5 to 20	to 2.5	2.5 to 19	to 115	to 115	3	740

Soft Steel Material Curves

- Use**
- Curved cutting of soft steel material.
- Materials**
- Bimetal High-Speed Steel

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)		Q'ty Per Bag (sheet)	Weight (g/bag)
								Stainless Steel Materials	Soft Steel Material		
767-8886	0095-8186	¥2,633	¥2,600	24	95	0.9	29	Curved Lines to 5	Curved Lines to 3.5	5	100

Contact us: 0120-20-8822 <http://www.hitachi-koki.co.jp/powertools/>