

# Disc Papers (double-sided design)

For Disc Grinders, see p. 5-209 to 226

The number next to the logo mark indicates items in stock for each brand.

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

TRUSCO Stock 38,650 Items

## "GP Curved Surface Disc"



ComEco Chemical Content Inspection  
Com Drawing SDS



GP100R (alundum (for general metal))

Estimated Unit Price per Sheet  
¥864




GP100RZ (zirconia (for heavy polishing))

Estimated Unit Price per Sheet  
¥864



One blade is rectangular and moderate rounded curvature (curved surface), so it is an excellent one that adapts to a curved surface.

- Features**
- Easy to bend because it uses polished cloth with rounded corner, even with small round surface, grinding work can be done easily.
  - Since the pad is small and has cushioning properties, there is no worry of deep scraping, and it fits perfectly on the uneven surface.
  - Very economical since it can be used up to the base of the pad.
  - Professional abrasive which is planted one by one by hand and caulked.
- Use**
- Paint removal, polishing before plating. Optimum for polishing stainless steel, iron, alloy, wood, plastic, etc.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
  - Japan



### Alundum (for general metal)

Specs • For general metal

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-9113	GP100R	100	¥4,318	¥5,330	100	100 x 25 x 15	13600	4 x 18	5	20	480
114-9121	GP100R	120	¥4,318	¥5,330	120	100 x 25 x 15	13600	4 x 18	5	20	480
114-9130	GP100R	150	¥4,318	¥5,330	150	100 x 25 x 15	13600	4 x 18	5	20	465
114-9148	GP100R	180	¥4,318	¥5,330	180	100 x 25 x 15	13600	4 x 18	5	20	465
156-9392	GP100R	240	¥4,318	¥5,330	240	100 x 25 x 15	13600	4 x 18	5	20	450
156-9406	GP100R	320	¥4,318	¥5,330	320	100 x 25 x 15	13600	4 x 18	5	20	450
156-9414	GP100R	400	¥4,318	¥5,330	400	100 x 25 x 15	13600	4 x 18	5	20	440


TRUSCO NAKAYAMA CORPORATION

### Zirconia (for heavy polishing)

Features • Use zirconia type good for abrasive materials for grinding operation.

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-9156	GP100RZ	40	¥4,318	¥5,330	40	100 x 25 x 15	13600	2 x 18	5	20	520
114-9164	GP100RZ	60	¥4,318	¥5,330	60	100 x 25 x 15	13600	3 x 18	5	20	560
114-9172	GP100RZ	80	¥4,318	¥5,330	80	100 x 25 x 15	13600	3 x 18	5	20	530



Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

## "GP 3-surface Disc"



ComEco Chemical Content Inspection  
Com Drawing SDS



GP1003F: 180 (alundum (for general metal))

Estimated Unit Price per Sheet  
¥864

- Features**
- Can be widely used for simple grinding work to grinding and polishing work.
  - Because the polishing cloths are folded into V shapes and attached to the pad, polishing work is possible with the 3 sides of the top, bottom, and side.
  - Very economical since it can be used up to the base of the pad.
  - Professional abrasive which is planted one by one by hand and caulked.
- Use**
- Polishing of metal tanks and various bead removal.
  - Ideal for polishing of various grooves.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
  - Japan

### Alundum (for general metal)

Use • Polishing of metals.

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-9237	GP1003F	100	¥4,318	¥5,330	100	100 x 20 x 15	13600	3 x 18	5	20	530
114-9245	GP1003F	120	¥4,318	¥5,330	120	100 x 20 x 15	13600	3 x 18	5	20	500
114-9253	GP1003F	150	¥4,318	¥5,330	150	100 x 20 x 15	13600	3 x 18	5	20	500
114-9261	GP1003F	180	¥4,318	¥5,330	180	100 x 20 x 15	13600	3 x 18	5	20	485
156-9422	GP1003F	240	¥4,318	¥5,330	240	100 x 20 x 15	13600	3 x 18	5	20	485
156-9431	GP1003F	320	¥4,318	¥5,330	320	100 x 20 x 15	13600	3 x 18	5	20	475
156-9449	GP1003F	400	¥4,318	¥5,330	400	100 x 20 x 15	13600	3 x 18	5	20	460

TRUSCO NAKAYAMA CORPORATION



Video

### Zirconia (for heavy polishing)

Features • The zirconia type has a good bite on the material being ground.  
Use • Grinding and polishing of non-ferrous metals such as stainless steel.

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-9270	GP1003F	40	¥4,318	¥5,330	40	100 x 20 x 15	13600	2 x 18	5	20	650
114-9288	GP1003F	60	¥4,318	¥5,330	60	100 x 20 x 15	13600	2 x 18	5	20	520
114-9296	GP1003F	80	¥4,318	¥5,330	80	100 x 20 x 15	13600	2 x 18	5	20	450



Contact us: 0120-509-849 <http://www.orange-book.com/>